





- 1 FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.
- 2 SWITCH SHOWN IN OPEN POSITION.
- 3 ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.
- 4 STAMPING WILL VARY ON 2 AND 3 POSITION TOPS DUE TO SPACE RESTRICTIONS.
- 5 STRIPPABLE TRANSPARENT SEAL, SEE FIG 6.
- 6 .315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300^{+0.010}/_{-.000} AT MOUNTING SURFACE.



CONTACT ARRANGEMENT





FIG 2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 9-19-89 CHK R. MILLER 9-19-89		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD H. LEITER 9-19-89 NAME SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED	
MATERIAL HOUSING & ROCKERS; POLYESTER CONTACTS: BERYLLIUM COPPER		FINISH CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL		SIZE A2	
WEIGHT -		APPLICATION SPEC -		CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO C-435802		RESTRICTED TO -	
SCALE 4:1		SHEET 1 of 2		REV A1 2	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		—	SEE SHEET 1	—	—	—




FIG 3A




FIG 3B




FIG 4





FIG 5



PROTECTIVE SEAL
FIG 6





FIG 7



PROTECTIVE SEAL




FIG 8

.010±.010

.005^{+.010}_{-.005}
TYP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 9-19-89	 TE Connectivity							
DIMENSIONS: INCHES		CHK R. MILLER 9-19-89								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD H. LEITER 9-19-89		NAME SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED					
			PRODUCT SPEC							
			APPLICATION SPEC							
		ANGLES ± ±		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		WEIGHT —		A2 00779 C-435802		—		
CUSTOMER DRAWING						SCALE 4:1		SHEET 2 of 2		REV AL2