

Datasheet

Steel Zinc Toggle Latch, Spring Loaded 100kg Op. Tension

RS Stock number [197-4160](#)



Description:

Base plate has slotted fixing holes for positional adjustment.

Latch can be utilised for gripping in groove without use of catch plate. Curved link gives wider tolerance

Suitable for medium duty applications

Zinc plated steel

Suitable for screw fixing using 2xM5 screws for latch and 2xM4 screws for catch 100kgf operating tension

Latch to catch distance 58.7mm

Features:

- Adjustable Yes
- Dimensions 93 x 47.5 x 20mm
- Finish Zinc Plated
- Material Steel
- Operating Tension 100kgf

