





NUMBER C-179019



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-1010-3C
REV. 3/93PC BOARDED DIMENSION
プリント基板取付穴寸法(THK)
板厚: 1.6±0.15
(TOL)
公差: ±0.1材質: 紙フェノールは推奨しない
MATERIAL: PAPER BASE PHENOLIC RESIN IS UNCOMMENDABLE

NOTES:

- △ TO BE MEASURED BETWEEN [A] AND 2
- △ TO BE MATED WITH PLUG HSG SMOOTHLY
- 3 TO BE USE M3 TAPPING SCREW JIS B1115 OR 1122 (TYPE2 OR 4) BEFORE SOLDER (TIGHTENING TORQUE, 0.8N-m (8Kg-cm) MAX)
- 4 APPLIED PLUG HSG P/N ; 173852

注:

- △ EAB面から2mmの範囲で測定
- △ 相手ハウジングと所定の機能を満たして嵌合できること
- 3 プリント基板への取付けは JIS-B1115又は1122, M3X6ナベ (2種又は4種) のタッピンネジで締付けた後ハンダ付けする (締付トルク: 0.8N-m (8Kg-cm) 以下)
- 4 嵌合相手ハウジング型番: 173852

				Copyright ©1993 AMP (Japan), LTD. ALL RIGHTS RESERVED.		Copyright ©1993 AMP (Japan), LTD. ALL RIGHTS RESERVED.		AMP 日本エー・エム・ピー株式会社 Tokyo, Japan	
				白 (WHITE)		錫めつき済 (PRE-TINNED)		1-179019-1	
				色 (COLOR)		コンタクト仕上り (FINISH OF CONTACT)		型番 (P/N)	
				ハウジング: PBT HOUSING		仕上げ (FINISH) 表参照 SEE TABLE		名称 (NAME) .070 SRS MLC 14Pos. CAP HSG (W-B(V-TYPE))	
				コンタクト: 黄銅 CONTACT BRASS		色 (COLOR) 表参照 SEE TABLE		.070シリーズ マルチロックコネクタ 14極 垂直型キャップハウジングアッセンブリ	
				A 変更 (REVISED) FJ00-0315-93 NY DA 4/2/93		一般公差 (GENERAL TOLERANCE)		一級公差 (PRECISION TOLERANCE)	
				O 作成 (RELEASED) FJ00-0236-93 HY KA 4/5/93		100μm ±0.2		100μm ±0.25	
				LTR 変更 (REVISION RECORD) DR CHK DATE		300μm ±0.3		300μm ±0.3	
				DR. N. Yamaguchi 4/5/93		角 度: ±3°		角 度: ±3°	
				CHK. R. Ogawa 4/5/93		APP. D. Sanita 4/5/93		B J C-179019	
								尺取 (SCALE) 2-1	
								REV. A	
								SHEET 1 OF 1	

(CUSTOMER DRAWING) 参考図面