






CABLE LENGTH TOLERANCE
UPTO 5m ±25mm ABOVE 5m ±50mm
GENERAL CABLE TOLERANCES UNLESS OTHERWISE STATED



PART No MATRIX



Specification.

Insert Material – PUR (30% Glass Filled)

Contact Material – Brass (CuZn36)

Contact Plating – 2um Ni, 0.70um Gold

Locking Ring — Brass Nickel Plate

Seal – Viton O-Ring

Protection Class – IP68


Voltage Rating – 3+4 Pole 250V: 5 Pole 60V

Contact Current Rating — 4 Amps

Overmoulding – PUR

Cable		Locking Ring Material	Overmould
E85	PVC BLACK-0.34mm	Nickel Plated Brass	PUR
A52	PVC BLACK-0.25mm	Nickel Plated Brass	PUR
P03	PUR BLACK-0.34mm	Nickel Plated Brass	PUR
P02	PUR BLACK-0.25mm	Nickel Plated Brass	PUR
K05	TPE YELLOW-0.25mm	Nickel Plated Brass	PUR

N/A	A	NW	NEW ISSUE	14.02.05	NW
ECN	Rev	By	Descriptions	Date	Approved



Third Angle Projection

This drawing and its contents are the proprietary and confidential property of Woodhead Industries Inc. and/or its subsidiaries and may not be used or disclosed to others without the express prior written consent of Woodhead Industries Inc. and/or its subsidiaries.

Applicable Standards ASME Y14.5M ISO 1660		
	NAME	DATE
Drawn	N WITTS	14.02.05
Checked	N.WITTS	14.02.05
Approved	N.WITTS	14.02.05

Material	SEE SPECIFICATION

Finish	SEE SPECIFICATION
--------	-------------------

Dimensions In MM
0.0 ± 0.25mm
0.00 ± 0.10mm
0.000 ± 0.025mm
Angles ± 1°

Part No.	Size
W0X006XXXMXXX	A4

D	Description	Part
E	ULTRA-LOCK SERIES	
	MALE STRAIGHT	

Drawing No.	Rev
WOX006XXXMXXX	A

Scale	NTS	SHEET 1 OF 1
--------------	-----	--------------