

QUICK CAB PCQ 604027 G



Sample photo

Order symbol: CAB PCQ 604027 G
Product nbr: 8113478
Description: Cabinet, PC
Remarks: Grey cover

EAN: 6418074011206
El. number:
 Finland: 3421980
 Italy: 7681065
 Sweden: 2540105
 Norway:

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	270	Ingress Protection (EN 60529): IP 66/67
inch:		23.6	15.7	10.6	Impact Resistance (EN 62262): IK 08
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		RAL 5023			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKIV 64H		Mounting plate			
EKIV 37		DIN-35 Mounting rail			
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			
PAT 12040		Hinge set			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Fimko			
		Lloyds Register of Shipping (LR)			
		Europe EN 62208: 2003			
		UL Canada			
		Gost R			

