




2 ハウジング全面にテフロン塗装のこと

OBSOLETE		20	67	58	48.29	41.29	49.2	18.4	4	9	178803-8
											5-178803-7
		16	59	50	40.67	33.67	41.6	18.4	4	7	178803-7
		12	51	42	33.05	26.05	34	18.4	4	5	178803-6
		10	47	38	29.24	22.24	30.2	18.4	4	4	178803-5
		6	40	31	21.62	14.62	22.6	8.4	2	2	178803-3
FINISH	POS. 極数 寸法 DIMENSION	A	B	C	D	E	F	G	N	型番 PART NUMBER	

										 TE Connectivity				
					抱合電線断面(WIRE RANGE) $\frac{\text{mm}^2 \text{ (AWG)}}{\text{mm}^2}$					被覆外径(INSULATION DIA.) $\text{mm} \phi$				
					材料(MATERIAL) 注記参照 SEE NOTES					仕上(FINISH)				
E2					REVISED PER EC0-11-005030					RK HMR 23MAR 11				
LTR					変更 (REVISION RECORD)					DR CHK DATE				
					DR. 4 MAR '92 N. Matsubara					DE. 4 MAR '92 N. Matsubara				
					CHK. 4 MAR. '92 H. ORATA					APP. 5 MAR. '92 S. MANABE				
					名称(NAME) パネルマウント タイプ タブハウジング ダイナミック 3100 シリーズ用 WIRE TO WIRE PANEL MOUNT TYPE TAB HSG FOR DYNAMIC 3100(DOUBLE ROW)					一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10を超え30以下: ±0.25 30を超え100以下: ±0.3 角度: ±3°				
					SIZE A3 LOC J					番号(No.) C-178803				
					尺屋(SCALE) 2/1					REV. E2				
										SHEET 1 OF 1				