

Standard handles & shafts

Disconnect
switches
Fusible



OHBS2AJ1




OHB_J6



OHY_J6



OHB4



OHM125L12

Recommended handles & shafts

Switch	Shaft diameter	Recommended standard pistol handle length	Maximum recommended shaft length
OS30 - 100	6x6 mm - .24 x .24"	45 - 65 mm	290 mm
OS200	6x6 mm - .24 x .24"	65 - 80 mm	290 mm
OS400 - 600	12x12 mm - .47 x .47"	125 - 175 mm	595 mm
OES800	12x12 mm - .47 x .47"	125 - 175 mm	595 mm

Selector handles — for use with .24 x .24" (6mm) OXS6X shafts ② ③

UL/NEMA Type	IEC type	Color	Marking		Defeatable	Padlockable	Weight (lbs)	Catalog number	List price
1, 3R, 12	IP65	Black	O/I & Off/On		—	Yes	0.16	OHBS2AJ1	\$ 28
					Yes	Yes	0.16	OHBS2AJ	30

NOTE: Selector handles are not recommended for use with fusible switches over 30A.

Pistol handles — for use with .24 x .24" (6mm) OXP6X shafts ② ③

UL/NEMA Type	IEC type	Color	Marking	Length in/mm	Defeatable	Padlockable	Weight (lbs)	Catalog number	List price
1, 3R, 12	IP65	Black	O/I & Off/On	2.6/65	Yes	Yes	0.29	OHB65J6	\$ 80
1, 3R, 12	IP65	Black	Off/On/Test	2.6/65	Yes	Yes	0.29	OHB65J6T ①	100
1, 3R, 12	IP65	Black	O/I & Off/On	3.1/80	Yes	Yes	0.30	OHB80J6	90
1, 3R, 12, 4, 4X	IP66	Black	O/I & Off/On	3.1/80	Yes	Yes	0.30	OHB80L6	130
1, 3R, 12, 4, 4X	IP66	Stainless Steel	O/I & Off/On	2.6/65	Yes	Yes	1.60	OHM65L6	750
1, 3R, 12	IP65	Black w/ stainless hasp	O/I & Off/On	2.6/65	Yes	Yes	0.31	OHB65J6EH	250
1, 3R, 12, 4, 4X	IP66	Black w/ stainless hasp	O/I & Off/On	2.6/65	Yes	Yes	0.31	OHB65L6EH	290

Pistol handles — for use with .47 x .47" (12mm) OXP12X shafts ② ③

UL/NEMA Type	IEC type	Color	Marking	Length in/mm	Defeatable	Padlockable	Weight (lbs)	Catalog number	List price
1, 3R, 12	IP65	Black	O/I & Off/On	4.9/125	Yes	Yes	0.39	OHM125J12	\$ 90
				5.7/145	Yes	Yes	0.39	OHB145J12	90
				6.9/175	Yes	Yes	0.41	OHB175J12	100
1, 3R, 12, 4, 4X	IP66	Black	O/I & Off/On	5.7/145	Yes	Yes	0.39	OHB145L12	130
1, 3R, 12, 4, 4X	IP66	Black	O/I & Off/On	6.9/175	Yes	Yes	0.41	OHB175L12	140
1, 3R, 12, 4, 4X	IP65	Metal	Off/On	8.7/220	--	Yes	1.50	YASDA-8	190
1, 3R, 12, 4, 4X	IP66	Stainless Steel	O/I & Off/On	4.9/125	Yes	Yes	1.70	OHM125L12	900
				6.9/175	Yes	Yes	1.80	OHM175L12	1,100
				275	Yes	Yes	2.10	OHM275L12	1,200
1, 3R, 12	IP65	Black w/ stainless hasp	O/I & Off/On	4.9/125	Yes	Yes	0.44	OHB125J12EH	280
				6.9/175	Yes	Yes	0.76	OHB175J12EH	330
1, 3R, 12, 4, 4X	IP66	Black w/ stainless hasp	O/I & Off/On	4.9/125	Yes	Yes	0.44	OHB125L12EH	330
				6.9/175	Yes	Yes	0.76	OHB175L12EH	390

Direct mount handle ② ③


For use on	Description	Marking	Color	Padlockable	Weight	Catalog number	List price
OS30	No shaft required	O/I/Test	Black	Yes	0.10	OHBS5	\$ 60
OS60-100	No shaft required	O/I	Black	Yes	0.10	OHB4	60
OS200	No shaft required	O/I	Black	Yes	0.30	OSV200BK	134
OS400	No shaft required	O/I	Black	Yes	0.30	OSV400BK	173
OS600	No shaft required	O/I	Black	Yes	0.30	OSV800BK	212
OS400-600, OES800	Mounts on 12mm shaft	—	Metal	No	0.78	YASDA-33	155

① The OS30 switch has a TEST position, accessed by rotating the mechanism 45 degrees counterclockwise from the OFF position. In the TEST position, optional auxiliary contacts, OA4B1C, are actuated but the main switch contacts are not.

② Red/Yellow handles are available by substituting the OHB prefix with OHY.

③ All handles are plastic unless otherwise noted as metal or stainless steel.

Standard handles & shafts



OXS6X_



OXP6X_
OXP12X_

Shafts — for use with OH selector handles .24 x .24" (6x6 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)	Weight (Lbs.)	Catalog number	List price
5.1 / 130	5.6	0.08	OXS6X130	\$ 6
7.1 / 180	6.1	0.11	OXS6X180	6
9.8 / 250	10.3	0.13	OXS6X250	12
13 / 330	13.4	0.17	OXS6X330	20

NOTE: Selector handles and shafts are not recommended for use with fusible switches over 30A

Shafts — for use with pistol handles .24 x .24" (6x6 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)				Weight (Lbs.)	Catalog number	List price
	OS30	OS60	OS100	OS200			
5.9 / 150	8.9	9.7	9.8	—	0.09	OXP6X150	12
8.3 / 210	9.7	12.1	12.2	9.9	0.13	OXP6X210	16
11.4 / 290	13.4	15.2	15.3	13.0	0.18	OXP6X290	20
14.2 / 360	18.7	12.9	18.0	—	0.23	OXP6X360	24
16.9 / 430	22.6	20.6	20.7	—	0.27	OXP6X430	28

Shafts — for use with pistol handles .47 x .47" (12x12 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)		Weight (Lbs.)	Catalog number	List price
	OS400	OS600, OES800			
11.0 / 280	13.8	14.9	0.77	OXP12X280	\$ 36
12.8 / 325	15.6	16.7	0.9	OXP12X325	40
15.6 / 395	18.3	19.4	1.1	OXP12X395	44
18.3 / 465	21.0	22.1	1.32	OXP12X465	48
21.1 / 535	23.8	24.8	1.54	OXP12X535	52