



ENGLISH

Datasheet

Stock No: 285-8766

RS Pro 15mm x 1/2 in BSPP Female 90° Tap Coupler Brass Compression Fitting



Product Details

Tap Connectors (Straight and Bent Patterns)

With BSP parallel threaded swivel nut

Sealing washer

Stock Numbers 285-8744 & 285-8750 are straight pattern

Stock Numbers 285-8766 & 285-8772 are bent pattern

Note

See 'Key characteristics' table for guide to pressure/temperature.

Fittings - Chrome Plated Brass

Chromium plated brass fittings.

Type A fittings suitable for mechanically joining metric o/d tubing in accordance with: Copper tube to BS2871: Part 1: Table X Table Z. Stainless steel tube to BS4127: Part 2: 1972.

For suitable chromium plated copper tube

BS864/2 BSI Kitemark Licence no. KM07082



ENGLISH

Key Characteristics			
Medium	Service Temperature up to		Max. Working Pressure
	°C	BAR	PSI
Water or light mineral oils 8 to 54mm sizes	30	16	230
	65	10	145
	110	6	87
	120	5	75
Compressed air non-shock 8 to 28mm sizes only	30	7	100
Saturated steam	120	3	4545
LPG & Natural Gas 8 to 28mm sizes only	30	1	15

Specifications:

Compression Connection Pipe Diameter	15mm
Fitting Type	Tap Coupler
Material	Brass
Threaded Connection	1/2 in BSPP Female
Fitting Direction	90°
Thread Size	1/2in
Thread Standard	BSPP
Gender	Female