

Datasheet

RS Pro Plain Stainless Steel Flat Head Machine Screws, M6 x 40mm

RS Stock No: **158-3556**



Product Details

RS Pro machine screw measuring M6 x 40 mm, is made of type 316 S16 plain A4 grade 18/8 stainless steel, which has higher level of corrosion resistance than A2 stainless steel. The flat head screw can be used at up to 300°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A4 grade 18/8 stainless steel (Type 316 S16) construction
- Higher level of corrosion resistance than A2 S/S
- Suitable for use up to 300°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	40 mm
Stainless Steel Type	316 (A4)
Thread Pitch	1
Thread Size (Metric)	M6
Head Diameter	10.87 to 11.3 mm
Head Height	3.3 mm
Slot Depth	1.2 to 1.6 mm
Slot Width	1.6 mm
Specification	DIN 963