

DESCRIPTION

PRODUCT COVERED:

USR, CNR Component - Terminal Blocks Model Nos. D35/27.FF
D70/32.FF, D120/42.FF, D185/55.FF and D300/55.FF

GENERAL:

These devices are provided with a stud and nut type terminations.

ELECTRICAL RATINGS:

Model No.	Max. Wire Size	Tightening Torque	Current Rating, A	Voltage Rating, V	Use Group
D35/27.FF	No. 1 AWG	-	125	600	B,C
D70/32.FF	No. 3/0 AWG	-	170	600	B,G
D120/42.FF	300 MCM	-	269	600	B,C
D185/55.FF	500 MCM	-	353	600	B,C
D300/55.FF	1000 MCM	-	460	600	B,C

B - Commercial appliances, including business equipment, electronic data processing equipment, and the like

C - Industrial, general

These devices are for factory wiring only.