

LOC		DIST		REVISIONS						
AJ		16		P	LTR	DESCRIPTION		DATE	DWN	APVD
					B1	REVISED PER ECO-11-005030		11MAR11	RK	HMR

- 1

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:NATURAL
- 2

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:BLACK
- 3

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4

ZINC PER QQ-Z-363.
- 5

PHOSPHOR BRONZE PER QQ-B-750.
- 6




BRASS PER ASTM-B-453.
- 7

NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 8

TIN PLATE PER ASTM-B-545, 3.81 μ m [.000150] MINIMUM THICK.
- 9

GOLD PLATE PER MIL-G-45204, 0.76 μ m [.000030] MINIMUN THICK.
- 10

SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT

PCB CONFIGURATION

9	2	5226990-6
9	1	5226990-3
8	1	5226990-1
CONTACT PLATING	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA — DOCK5	20APR2005	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. HAVENER	20APR2005	NAME	
		APVD S. BURKHOLDER	20APR2005	JACK, PANEL, RIGHT ANGLE, 50 OHM, PCB, SERIES BNC	
		PRODUCT SPEC	108-12078		
		APPLICATION SPEC	—		
MATERIAL 1 THRU 6	FINISH 7 THRU 9	WEIGHT	—	SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 1
		REV	B1		