

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, — .

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

—

J

J1

J2

ECR-09-000314

REVISED PER ECO-09-023313

ECR-10-026542

21-05-09

12OCT09

05JAN11

AEG

KK

KK

KMA

AEG

HMR

5,0 HEX

GROOVE TO INDICATE M3 INNER THREAD

GROOVE TO INDICATE M3 OUTER THREAD

D REF.

4,8±0,1

A±0,1

C

B

1

OBSOLETE

1

OBSOLETE

10,8

9,8

19,0

12,7

DIM "D"

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

DIM "C"

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

4-40 UNC

M3

DIM "B"

6,0

5,0

5,0

5,0

5,0

14,2

14,2

14,2

7,9

7,9

7,9

7,9

DIM "A"

TINPLATED

BRASS

FINISH

3-829261-0

2-829261-8

2-829261-6

2-829261-4

2-829261-2

1-829261-8

1-829261-6

1-829261-4

1-829261-2

829261-8

829261-6

829261-4

829261-2

MATERIAL

829261-0

829261-8

829261-6

829261-4

829261-2

829261-8

829261-6

829261-4

829261-2

829261-8

829261-6

829261-4

829261-2

PART NUMBER

1

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING

PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0,2

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ±

MATERIAL

-

FINISH

-

DWN

D.KESSLER

02APR91

CHK

C.V.TILBURG

23APR91

APVD

L.V.SOEST

25APR91

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

STE

TE Connectivity

NAME

SCREWLOCK, FEMALE HD-SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-829261

—

SCALE

NTS

SHEET

1 OF 1

REV

J2

1470-19 (3/11)