

FEX FEX 2828 18 G



Sample photo

Order symbol: FEX 2828 18 G
Product nbr: 4130813
Description: Enclosure, PC
Remarks: Ex e II, EN 60079; IK 4J

EAN: 6418074008015
El. number:
Finland: 3424660
Denmark: 8212026405
Italy: 7801145
Sweden: 4130813
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		278	278	180	Ingress Protection (EN 60529): IP 54
inch:		10.9	10.9	7.1	Impact Resistance (EN 50014): 4J
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Certificates:
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Silicone			
Temperatures:					ATEX
Short term:		-40 ... 120 °C			EC Certificate of Conformity
Continuous:		-10 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		14 ... 175 °F			
Accessories:					
EKHVT		Mounting plate			
EKJVT		Mounting plate			
EKMVT		Mounting plate			
EKOVT		Mounting plate			
EKPVT		Mounting plate			
EKTVT		Mounting plate			
EKUVT		Mounting plate			
EKV 12		DIN-35 Mounting rail			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			

SOLID 278x278x130-180

