



D




- HOUSING: PBT, UL94V-0, COLOR BLACK.
- POSTS: PHOSPHOR BRONZE.
- POSTS: 0.00038[.000015] MIN GOLD ON MATING AREA, 0.00254[.000100] MIN TIN ON SOLDER END, ALL OVER 0.00127[.000050] MIN NICKEL ON ENTIRE POST.
- DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.
- NO KEYING SLOT ON THIS END FOR 6, 8, 10, 12 & 14 POSITION ASSEMBLIES.
- NO KEYING SLOT ON THIS END FOR 6, 8 & 10 POSITION ASSEMBLIES.

C



B



A

RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

OBSOLETE	73.66 [2.900]	29	81.28 [3.200]	83.82 [3.300]	60	1-1761602-6
	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	1-1761602-5
	53.34 [2.100]	21	60.96 [2.400]	63.50 [2.500]	44	1-1761602-4
	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	1-1761602-3
	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	1-1761602-1
	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	1761602-9
	27.94 [1.100]	11	35.56 [1.400]	38.10 [1.500]	24	1761602-8
	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	1761602-7
	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	1761602-6
	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	1761602-5
	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	1761602-3
	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

MATERIAL

DWN J. GERACE 13JAN05
CHK S. BOLASH 13JAN05
APP'D M. WALMSLEY 13JAN05
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

tyco
Electronics
Tyco Electronics Corporation
Harrisburg, Pa 17105
NAME
HEADER ASSEMBLY, VERTICAL,
LOW PROFILE, IDC
SIZE CAGE CODE DRAWING NO
A1 00779 1761602
RESTRICTED TO

CUSTOMER DRAWING
SCALE 4:1
SHEET 1 OF 1
REV B