

Datasheet

## **RS Pro 40W/m Trace Heating Kit Constant Wattage, Parallel Circuit, 240 V, 20m**

RS Stock No: **379-750**



### **Product Details**

RS Pro parallel circuit trace heating kit is 20 m long and provides 40 W/m constant wattage output. The trace heating kit has a voltage rating of 240 V. This parallel circuit heating tape with a constant wattage output is suitable for process temperature maintenance applications. The tape is flexible enough to allow it to be spiralled around a suitable pipe or vessel. The parallel circuit heating tape meets BS En 62395-1:2006 standards.

### **Features and Benefits**

- The outer sheath is notched on alternate sides at 1 m intervals to indicate cutting points
- For internal or external temperature maintenance applications
- Freeze protection
- Water, oil and chemical lines
- Sprinkler system mains
- Supply piping

**Specifications:**

Cable Type	Constant Wattage, Parallel Circuit, Trace Heating
Hazardous Area Certification	No
Length	20 m
Maximum Operating Temperature	+200°C
Minimum Operating Temperature	-60°C
Operating Temperature Range	-60 to +200°C
Output per Metre	40 W
Sheath Material	Silicone Rubber
Standards Met	BS EN 62395-1:2006, RoHS Compliant
Voltage Rating	240 V