

28W47 Watertight NEMA 4X/6P Locking Plug, Yellow

28W47



Locking Watertight Plug, 30amp 125volt, NEMA Configuration L5-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.



features & benefits

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

specifications

General Info

Color: yellow
Type: Plug
Features: Watertight
Number Of Poles: 2
Number Of Wires: 3
Special Features: Watertight, NEMA

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 42M
CSA Standard: Yes
UL Listing No: UL498

UL Standard: Yes
UN SPS C: 39121403

Dimensions

Diameter U S: 2.50"
Length U S: 3.11"

Technical Information

Amps: 30 Amp
Material: Rubber
NEMA Configuration Number: L5-30
NEMA Rating: 4X/6P
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant