


Housing - HC-B 16-SML-67/O2PG21 - 1673708

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base with single locking latch, height 67 mm with support 2x PG21

Key commercial data

Packing unit	10 pc
GTIN	 4 017918 152529
Weight per Piece (excluding packing)	330.17 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	67 mm
Width	57 mm
Length	117 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K
Type	B16
Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable outlets	2
Cable exit	Lateral
Screw connection	none
Type of the screw connection	2x Pg21
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

Housing - HC-B 16-SML-67/O2PG21 - 1673708

Technical data

General

Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA
Assembly instructions	For half and full screw connections

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC002498
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Housing - HC-B 16-SML-67/O2PG21 - 1673708

Approvals

Approval details

EAC

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG21-M68N-PNES-GY - 1411145



Cable gland, Cable gland material: Polyamide, External cable diameter 13 mm ... 18 mm, Shielding: No, Connecting thread: Pg21, Color: silver grey

Cable gland - G-INS-PG21-M68N-NNES-S - 1411175



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 13 mm ... 18 mm, Shielding: No, Connecting thread: Pg21, Color: silver

Cable gland - G-INSEC-PG21-M68N-NNES-S - 1411200



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 13 mm ... 18 mm, Shielding: Yes, Connecting thread: Pg21, Color: silver

Plug for cable screw gland

Filler plugs - HC-BS-PG21 - 1674529




Filler plugs, for Pg screw connections, type Pg21

Drawings

Housing - HC-B 16-SML-67/O2PG21 - 1673708

Dimensioned drawing



Dimensional drawing; h = 67 mm

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>