



STRIPPING DIMENSION
SCALE 4:1



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-10 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 335 VOLTS MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
4.2 FOR USE WITH RG174U OR SIMILAR STYLE CABLE
4.3 CABLE ATTACHMENT: OUTER: CLAMP, INNER: SOLDER

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -85° C TO +165° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
6	CENTER CONTACT	BRASS	1	GOLD 30 μ" MIN.
5	NUT	BRASS	1	GOLD 3 μ" MIN.
4	WASHER	BRASS	1	GOLD 3 μ" MIN.
3	SLEEVE	BRASS	1	GOLD 3 μ" MIN.
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	GOLD 3 μ" MIN.



APPROVED

by _____ DATE: _____

DESCRIPTION			SMC STRAIGHT PLUG CLAMP									
製圖	DRAWN	TOLERANCE		品名	26-15	T.G.N	174U	日期	DATE	版次	REV.	
	Kristina	X	±0.2	TITLE	ROHS COMPLIANT (50μ)				03.05.15	A-0		
檢圖	CHECK	XX	±0.1	單位	UNIT	DWG.NO. 26-0025						
	Arc				mm(in)							
認定	APPROVAL	XXX	±0.05	比例	SCALE							
	Angela				ANGLE ±5°							4:1