





A

B

C

D



Connector pitch on panel:
Axis X = 27 mm and Axis Y = 21 mm
Receptacle mating side according to
600076-3-106 IEC - variant 04

Mating references A and B
according to IEC 60603-7

(1) Screwing x2 M2.5 screws between 0.5N.m and 0.8N.m
screw according to DIN 912 and ISO 4762

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Push pull RJ Industrial black Thermoplastic IP67 Receptacle With overmolded flat Seal	Maßstab/ Scale 1,5:1
			Detail.	12/01/10	AB			
			Insp.	14/06/11	JMV			
36243	14/06/11	AB	Stand.				TB 09 45 545 00 29	Blatt/ Page 1/1
36092	05/09/10	AB						
EC01204	12/01/10	AB						
Mod.	Dat.	Name					Sub.	

HARTING EURL
F-95972 Paris