



Issue	Description	Date
A	新图	2011/10/06
B	更換IC盒子/接線圖	2013/08/20




WIRING:

有IC面(正面)



无IC面(反面)



地(ground)

- | | | |
|----|-----------|----|
| 19 | 白(white) | 19 |
| 14 | 黑(black) | 14 |
| 17 | 地(ground) | 17 |
| 1 | 白(white) | 1 |
| 3 | 紅(red) | 3 |
| 2 | 地(ground) | 2 |
| 4 | 綠(green) | 4 |
| 6 | 白(white) | 6 |
| 5 | 地(ground) | 5 |
| 7 | 棕(brown) | 7 |
| 9 | 白(white) | 9 |
| 8 | 地(ground) | 8 |
| 10 | 藍(blue) | 10 |
| 12 | 白(white) | 12 |
| 11 | 地(ground) | 11 |
| 13 | 紅(red) | 13 |
| 15 | 灰(gray) | 15 |
| 16 | 白(white) | 16 |
| 18 | 橙(orange) | 18 |

- | | | |
|----|-----------|----|
| 19 | 白(white) | 19 |
| 14 | 黑(black) | 14 |
| 17 | 地(ground) | 17 |
| 1 | 白(white) | 1 |
| 3 | 紅(red) | 3 |
| 2 | 地(ground) | 2 |
| 4 | 綠(green) | 4 |
| 6 | 白(white) | 6 |
| 5 | 地(ground) | 5 |
| 7 | 棕(brown) | 7 |
| 9 | 白(white) | 9 |
| 8 | 地(ground) | 8 |
| 10 | 藍(blue) | 10 |
| 12 | 白(white) | 12 |
| 11 | 地(ground) | 11 |
| 13 | 紅(red) | 13 |
| 15 | 灰(gray) | 15 |
| 16 | 白(white) | 16 |
| 18 | 橙(orange) | 18 |

IN PUT
(接DVD播放機)

TV OUT PUT
(接TV電視機)

壳(shell)

壳(shell)

G.						All Dimensions are Millimeters				Approved	Checked	Drawn		力代 FIRST TECH ELECTRONICS CO.,LTD(TAIWAN) TEL:886-6-2720201-3 FAX:2720607 Website: www.firsttech.com.tw	
F.						Unless Otherwise Specified Tolerances						黃天海 2013/08/20		祥發 HSIANG FA ELECTRONIC PLASTIC FACTORY(CHINA) TEL:86-755-29715311-3 FAX:29715767	
E.	SCREW	4		NICKEL		0.5~6= ±0.1								客户	700=7424337
D.	STOPPER	1	PVC	BLACK		6~30= ±0.3				祥发	CB-HD-001G-IC-CH67AL-28#+15M				
C.	DUST PROOF COVER	2	PVC	TP		30~120= ±0.5				TITLE	HDMI PLUG TO HDMI PLUG +IC				
B.	BODY	2	PVC	BLACK		120~315= ±0.8				CABLE	CH67AL-28# (1P*28#+AEM)*5C+4C*28#+AB OD:7.3mm				
A.	HDMI PLUG	2	BRASS	GOLD		ANGLES= ±3°									
NO	Description	Unit	Materials	Finish/Color	PART NO.	Scale	1:1	Issue	A						

