








LOC I	DIST —	REVISIONS REVISIONI						
		P	LTR REV	DESCRIPTION DESCRIZIONE	DATE DATA	DWN DIS	APVD APP.	
			—	SEE SHEET 1	—	—	—	



DETT. CONTATTO SC. 5:1
 (TAB DETAIL SC. 5:1)



✓FORMA ALTERNATIVA PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)



SPIGOLI VIVI
(SHARP EDGE)

- 1) QUOTE APPLICABILI PER SFORMATURA PEZZO
(RIGHT DIMENSIONS FOR EXTRACTION ITEM
FROM THE MOULD)
- 2) MATERIALE CONTATTI: LEGA DI RAME STAGNATA,
ES. OTTONE STAGNATO.
(TAB MATERIAL: TINNED Cu ALLOY,
E.G. TINNED BRASS)
- 3) MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO
FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC
GLASS FIBER FILLED).

3.0	GIALLO (YELLOW)	—
12.0	NATURALE (NATUR)	—
10.2	BLU (BLUE)	—
4.8	MARRONE (BROWN)	—
6.6	VERDE (GREEN)	—
8.4	GRIGIO (GREY)	—
” X ”	COLORE BLOCCETTO (HOUSING COLOUR)	NOTE (NOTES)

METRIC		THIS DRAWING IS A CONTROLLED DOCUMENT. QUESTO DISEGNO E' UN DOCUMENTO CONTROLLATO.		DWN / DIS.	—	TE Connectivity					
		DIMENSIONS: DIMENSIONI: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLLERANZE SE NON DIVERSAMENTE SPECIFICATO	APVD / APP.	—			NAME NOME			
			0 PLC / DEC. ± — 1 PLC / DEC. ± 03 2 PLC / DEC. ± — 3 PLC / DEC. ± — 4 PLC / DEC. ± — ANGLES / ANGOLI ± 2°	PRODUCT SPEC SPEC DI PRODOTTO	—						
				APPLICATION SPEC SPEC DI APPLICAZIONE	—						
DIAM. ISOLANTE (INS. DIA. RANGE) SEE SHEET 1	RANGO FILO (WIRE RANGE) SEE SHEET 1	MATERIAL MATERIALE	FINISH FINITURA	WEIGHT PESO	—	A3	00779	DRAWING NO NUMERO C=282680	(MASTER)	RESTRICTED TO	—
CUSTOMER DRAWING				DISEGNO PER CLIENTE SOLA PER DIFFERIMENTO		SCALE SCALA	—	SHEET FOGLIO	2	OF 2	REV C1