



GPWV2.E38324 Fans, Electric - Component

[Page Bottom](#)

Fans, Electric - Component

[See General Information for Fans, Electric - Component](#)

EBM-PAPST ST GEORGEN GMBH & CO KG

E38324

VERWALTUNG UND WERK 1
HERMANN-PAPST-STR 1
78112 ST GEORGEN, GERMANY

Models RER-125, -160, RET 90-18/24, RG90, -125, -160.(DC).

Models RER125, -19/06, -19/56, RER160-28/06, -28/56, RG9-18/06, -18/56, RG125-19/06, -19/56, RG160-28/06, -28/56.(AC), with or without suffix U; Models RL90-18/50, -18/56, -18/06 with or without prefix RL.

Types W2K121-AA01, -AA15, -AA19, -AA51, -AB07, -AB11; Types 5900, 5908, 5938, 5950, 5958, 5988 with or without suffix W and/or U.

Model Series 412J, 414J; Model 412J or 414J followed by /S or /2 through 39, may be followed by H or HH, may be followed by R, may be followed by three digit suffix.

Models Series RER75-19/12 followed by /S or /2 through /39, may be followed by H, may be followed by T, I, A, P, R or U, may be followed by three digit suffix.

Series REF; Series RLF; Model REF100-11 or RLF100-11 followed 12, 14, 18, followed by /S or /2 through /39, may be followed by G, may be followed by H, R or U, may be followed by three digit suffix; Vario-Pro Series REF; Vario-Pro Series RLF; Model REF100-11 or RLF100-11 followed 12, 18, followed by /S or /2 through /39, may be followed by G, may be followed by H, may be followed by T, A, I, P or F, may be followed by R or U, may be followed by three digit suffix.

Series REF; Series RFL; Models REF100-11 or RLF100-11, followed 12, followed by /S or /2 through /39, may be followed by G, followed by 059, may be followed by R or U, may be followed by three digit suffix.

DC fans, Model Series 255, Model 255 followed by N, M or H, may be followed by numbers; Model Series 252, Model 252N.

Models DV6212, DV6224, DV6248 may be followed by a one or two digit suffix, may be followed by L, may be followed by T, may be followed by R, may be followed by U, may be followed by three digits; Models DV6212, DV6224, DV6248 may be followed by a one or two digit suffix, may be followed by L, M or H, may be followed by T, A, I or P, may be followed by R, may be followed by U, may be followed by three digits, followed by VARIO PRO@; Models DV6224 "SCP", DV6248/19P "TCF".

Models DV4112, DV4114, DV4118 may be followed by additional suffixes, Vario Pro, DV5212, DV5218 may be followed by 1,6,7,8 or 9, may be followed by 2, 4 or 8, may be followed one or two digit, followed N, may be followed by T, A, I or P, may be followed by R, U, may be followed by three digit suffix; DV5214 may be followed by 1,6,7,8 or 9, may be followed by 2, 4 or 8, may be followed one or two digit, followed N or H, may be followed by T, A, I or P, may be followed by R, U, may be followed by three digit suffix.

Model 422J/2_HP followed by R or U, followed by three digits, followed by ST1 or VP1.

DV5212, DV5218 may be followed by 1, 6, 7, 8 or 9, may be followed by 2, 4 or 8, may be followed one or two digit, followed N, may be followed by T, A, I or P, may be followed by R, U, may be followed by three digit suffix.

DV5214 may be followed by 1, 6, 7,8 or 9, may be followed by 2, 4 or 8, may be followed one or two digit, followed N or H, may be followed by T, A, I or P, may be followed by R, U, may be followed by three digit suffix.

Model RER72-17/14/2U.

Model RER100-5/14/2.

Models RER100-25/12, RER100-25/14 may be followed by additional suffixes.

Models RER100-28/18N/13TD, RER200-A5/18N/13TD, RET100-28/18N/13TD, RG-160-28/18N/13TD, RER160-28/18N/#TDH, RET160-28/18N/#TDH, RG160-28/18N/#TD#V, RER200-45/18N/#TD-624, -625, RG160-28/18N/#TDV, RG-160-28/18N/#TDTVU, RG160-28/18N/#HTDPV, RG160-28/18N/#HTDI, RER190-39/14/#TDL.

Models RER101-36/12/#H##, RER101-36/12/###, RER101-36/48/###, RER101-36/48/#H##, RER101-36/12N/##HH#, RER101-36/18N/##HH#.

Models(*) RER125-19/12N, -19/12NM, -19/14N, -19/14NM, -19/18N/2HV, RER160-28/12N, -28/12NM, -28/14N, -28/14NM, -28/18N/##H#, -28/18N/19T-155, RET90-18/12N, RG90-18/12N, -18/12N/17V, -18/14N, -18/18N, -18/18N/32HNR, RG125-19/12N, -19/12NM, -19/14N, -19/14NM, -19/18N, -19/NM, RG160-28/12N, -28/12NM, -28/14N, -28/14NM, -28/18N, -28/18NM, RL90-18/12N, -18/12N/2-410, -18/12N/2-415, -18/12N/2-416, -18/12SN, -18/14N may be followed by suffix U; Models Vario-Pro Series RER125-19/18N, RET125-19/18N, RG125-19/18N, RER125-19/18N, RET125-19/18N, RG125-19/18NH, RER; RET; RG-160-24/14...NP.

Models RER120-26/14/#TD, RER120-26/18/#TD, RER133-41/14/#TDM, RER133-41/18/#TD, RER133-41/18/#TDL, RER175-42/14/#TDML, RER175-42/18/#TDML, RER175-42/18/#TDM, RER175-42/18/#TDM, RER190-39/14/#TDML, RER190-39/14/#TDM, RER190-39/18/#TDML, RER190-39/18/#TDM, RER190-39/18/#TD, RER190-45/14/#TDML, RER190-45/18/#TDML, RER190-45/18/#TDM, RER225-55/18/#TDM, RER225-63/18/#TDM, RER225-63/18/#TDM.

Models RL90-18/12, RL90-18/24, RL90-18/24-017, 3112F, 3112FL, 3124F, 4112GSM-059, 4112GSMS-059, 4112GX, 4112GX-065, 4112GXL, 4112GXLS, 4112GXM, 4112GXM-059, 4112GXM-061, 4112GXMS, 4112GXMS-059, 4112GXMS-061, 4112GXS, 4112GXS-065, 4112KX, 4112KXS, 4112X, 4112XS, 4124GX, 4124GXM, 4124GXMS, 4124GXS, 4124KX, 4124KXS, 4124X, 4124XS, 4136/6KN, 4148X, 4148XS, 4148XP, 4148XPS, all models may be followed by suffix S, /2, /6 or /12, Third digit may be 6, 7, 8 or 9; Models 6124, 6148, 8112, 8112S, 8112K, 8112KS, 8112G, 8112GS, 8124, 8124G, 8124GS, 8124K, 8124KS, 8124S, 8148, 8148S.

Models RL133-50/2-7, RL133-50/2-8, RL133-50/2-6, RL133-50/2-9.

Models QG030-148/12, -148/14, -198/12, -198/14, -303/12, -303/14, -353/12, -353/14, RL VD-1-27.08(12V), RL VD-1-27.08(24V).

"Vario" Models 3312V, 3412GMV, 4312MI-082, 4312MV, 4312V, 8312MV, 8412GLV, 8412GMV, 8412GV may include suffixes G, L, M, R, 6, 7, 8, 9, /2, /6, /10, /12, /17 or /19.

Models W2K113-AA01, -AA15, -AB05, -AB07, -AD21, -AD31, W2K121-AA01, -AA15, 5900, 5908, 5950, 5958, 9530, 9538, 9580, 9586, 9600, 9608, 9650, 9658, 9800, 9808, 9850, 9858.

Models 900, 950, 970T, 970TR, 971TR.

Models 33X2, 33X4, 33X4H, 33X8, 33X8H, 83X2, 83X2H, 83X2L, 83X2LM, 83X2M, 83X2HL, 83X4, 83X4L, 83X4M, 83X4HL, 83X4H, 83X4HV, 83X8, 8318, 83X8HL, 83X8H, 33X2, 33X2H, 33X2L, 33X2M, 33X4, 33X4H, 33X4L, 33X4M, 33X6/6, 8312S may be followed by "G", "R", "S" or "U", may be followed by 6, 7, 8, 9, /2, /6, /10, /12 or /19, may be followed by additional three digit suffix, where X can be 1, 6, 7, 8 or 9; Models 33#2U-480, 3312U-026, 3312-552, 33#2U-024, 33#2U-557; Models 3318, 3318H, 8314H, 8314HH, 8318, 8312H, 8312HL, 8318H, 8314L, 8314HL, 3314, 3314H.

Model 41 followed by 1, 6, 7, 8 or 9, followed by 2, 4, 8, 9, followed by N or EN, may be followed by C, G, H, HH, L, LM, M, R, S or X, /2, /6, /10, /12, may be followed by "114", "115" or "116" or H; Models 4114N/12GH-159, 4119N/12GH-150; Vario Pro Series 41#4N, 41#8N; Model 41 followed by 1, 6, 7, 8 or 9, followed by 4 or 8, followed by N, may be followed by H, HH, H3 or X, may be followed by additional numbers, followed by Vario Pro.

Models 4114NVU-179, 4114NXHVU-184.

Model 44x2F may be followed by D, G or M, where x is 1, 8, 9; Model 44x4F or 44x8F may be followed by D, G, M, where x is 1, 8, 9; Model 3412 may be followed by G, H, L, M, /2, /17G1-144; Model 3414 may be followed by G, H, K, M, /2; Model 3418 may be followed by G, L, 12; Model 8412 may be followed by G, H, L, M; Vario Pro Model 4414F, 4418F may be followed by D, M, MD, may be followed by T, A, I, P, may be followed by R, U, may be followed by addition numbers, followed by Vario Pro.

Models 42#2L, 42#2M, 42#2, 42#2H, 42#4L, 44#4M, 42#4, 42#4H, 42#6, 42#8, 42#8C, 42#8H, 44#2L, 44#2M, 44#2, 44#4L, 44#4M, 44#4 may be followed by "E", "R", "S", "U", "V", /2, /6, /8, /10, /12, /17 or /19, may be followed by additional numbers, Third digit in type designation may be "1", "6", "7", "8" or "9".

Model 43X8, where "X" can represent 1, 6, 7, 8, 9; Models 4312, 4312/2, 4312GM, 4312GMVAR134, 4312GMVAR148, 4312L, 4312M, 4312M-047, 4312MS, 4312MVAR034, 4314, 4314L, 4314M, 4314-062, 4318, 4318/2, 4352M-069, 4362L, 4362M, 4362, 4372, 4374, 4378, 4382, 4392, 4392L, 4392M, 4394, 4394L, 4394M, 4398, 4312MI-082 may be followed by "D", "G", "R", "S", "U", "V", "6", "7", "8", "9", "/2", "/4", "/12", "/17", "/19", "/23" or "/28", may be followed by three digits; Vario-Pro Series, Models 4314, 4318, 4318H.

Model Series 46XX, 48XX with or without suffix U; Models 3910, 3911, 3960, 8551N, 8551N-360, 8551N-380, 8551N-384, 8551N-385; Models 8500, 8550, 8550N-380, 8560, 8580, 8581 with or without suffix D, DP or N; Models 8506, 8524, 8526, 8556, 8566, 8700, 8750, 8800, 8830, 8836, 8846, 8850, 8856, 8860, 8880, 8886, 8890 with or without suffix A, AW, D, N, R, T, TA, TV, V, VW or W.

Model Series 45XX, 46XX, 48XX with or without suffix U; Models 4250, 4700, 4750, 4840, 4860, 4890 with suffix B, H, N or X; Models 4500, 4530, 4536, 4550, 4580, 4586, 4590, 4600, 4601, 4606, 4608, 4612, 4624, 4650, 4656, 4658, 4660, 4666, 4800, 4806, 4850, 4856 with or without suffix A, AW, B, H, N, NW, T, V, VW, W, X, XP or Z or "ZW", may be followed by "411" or "413"; Models 4600N-381, 4650N-381, 4650N-382, 4650Z-877, 4656Z-935, 4850NVAR353; Model DV followed by 4500, 4530, 4550, 4580, 4600, 4606, 4550, 4656, 4800, 4840, 4850 or 4890.

Models 405, 405F, 405F-002, 405FH, 412, 412F, 412FH, 412FM, 412H, 412H-020, 414, 414F, 414FH, 414H, 505F, 512F, 512FH, 512FL, 514F, 514FH, 605F, 612F, 612FH, 612FL, 614F, 614FH may be followed by additional suffixes.

Series 600N, Models 612NG, 612NGL, 612NGML, 612NGM, 612NGN, 612NGH, 612NGHH, 612N#HH, 614NGL, 614NGML, 614NGM, 614NGN, 614NGH, 614NGHH, 614N/2M-047 may be followed by suffixes I, V; Models 614N#HH, 618N#N, 618N#M, 622#L, 622#M, 622#N, 622#H, 622#HH, 622#HHP, 624#L, 624#M, 624#N, 624#H, 624#HH, 624#HH#.

Models Series 3212J, 3214J, 3218J followed by /S or /2 through /39, followed by Blank, N, M, H, H3 or H4, may be followed by R, may be followed by three digit suffix; VarioPro Model Series 3212J, 3214J, 3216J or 3218J followed by /S or /2 through /39; followed by blank, N, M, H, H3 or H4; may be followed by D; followed by blank, T, I, A, P or F; may be followed by R or U; may be followed by 3 or 5 digits, may be followed by -199, also marked with name "VarioPro" or "VP1".

Models 605GMS, 605L, 605MS, 612, 612GI, 612GL, 612GMI, 612L, 612M, 612S, 614, 614L, 614M, 614S, 614S-024 may be provided with suffixes "G", "L", "R" or /10; Models 812, 812L, 812M, 814, 814L.

Models 34#2, 34#4 followed by 1 or 2 digit suffix; may be followed by L, M, H; followed by additional suffixes. Model 34#8, followed by 1 or 2 digit suffix; may be followed by L; followed by additional suffixes. Model 44#2, followed by 1 or 2 digit suffix; may be followed by F; may be followed by L, LL, M or ML; followed by additional suffixes. Model 44#4, followed by 1 or 2 digit suffix; may be followed by F; may be followed by L or M; followed by additional suffixes. Model 84#2, followed by 1 or 2 digit suffix; may be followed by L or M; followed by additional suffixes. Model 84#4, followed by 1 or 2 digit suffix; may be followed by L, M or H; followed by additional suffixes. Vario Pro Models 44#2F#, 44#4F#, 44#8F#.

Models Series 3412N, 3414N, 8412N, 8414N may be followed by /2, /9, /12, /19 or /28, may be followed by L, M, ML, H, HH or a blank, may be followed by E, G, I, R, V, P; Model 3412N#GHH#; Model Series 712F; Model Series 8418N may be followed by /2, /9, /12, /19 or /28, may be followed by H or a blank, may be followed by G, I, R, V.

Models 3500, 3506, 3550, 3556, 3600, 3606, 3650, 3656, 3660, 3666, 3800, 3806, 3850, 3856 with or without suffix E, H, R, T or U.

Models 3900, 3906, 3950, 3956, 9500, 9506, 9550, 9556, 9900, 9906, 9950, 9956 may be followed by M or L.

Models Series 4212N, 4214N, 4218N, 4296NH; Models 4312N, 4314N, 4318N may be followed by additional numbers and/or letters.

Models 5112, 5114, 5118 may be followed by letter "N"; Models 5192, 5194, 5198 may be followed by /2, /12.

Model 5212 followed by one or two digit suffix, followed by M, H or HH, followed by additional suffixes; Model 5414 followed by one or two digit suffix, followed by M, H or HH, followed by additional suffixes; Model 5814 followed by one or two digit suffix, followed by L, M, H or HH, followed by additional suffixes; Vario Pro Model 5414 followed by one or two digit suffix, followed by M, H or HH, followed by additional suffixes; Vario Pro Model 5814 followed by one or two digit suffix, followed by L, M, H or HH, followed by additional suffixes.

Models 5606S, 5656S.

Models 6202, 6202/2T, 6202M, 6202N/2M, 6202N/2MT, 6212/6M, 6212M, 6212N#H, 6224, 6224/2, -/3, -/4, -/5, -/6, -/8, -/9, -012, -/12, -017, 6224H, 6224L, 6224M, 6224MS, 6224N/4-185, 6224N/12HT-197, 6224N/12L-198, 6224N/12M-204, 6224S, 6226, 6226/6, 6236N/2L, 6236-013, -015, 6224N/8H-186, 6224N/8HT-205, 6224N/17HT-187, 6224N/17HT-201, 6248, 6248NL, 6248/2, -/3, -/3T, -/4, -/5, -006, -/6, -007, -008, -/8, -/8T, -009, -/9, -010, -011, -/11, -012, -/12, -014, -/15, -028, 6248M, 6248MS, 6248S, First four digits may be followed by "N"; Models 6402/2T, 6412, 6412/6M, -19T, 6424, 6424/2, -/3, -/4, -/5, 6424/6, -/8, -/9, -012, -/12, -017, 6424/8H-322, 6424/8H-331, 6424/17HT-328, 6424H, 6424L, 6424M, 6424MS, 6424S, 6426, 6436-013, -015, 6448/2, -/3, -/3T, -/4, -/5, -006, -/6, -007, -008, -/8, -/8T, -009, -/9, -010, -011, -/11, -012, -/12, -014, -/15, -/17, -/19T, -028, 6448M, 6448MS, 6448S, 6448/2HHT, First four digits may be followed by "N", "U"; Series VarioPro 62#N, 64#.

Models 7112, 7114, 7118 may be followed by letters "H", "N", "T", "/2", "/12" or "/19".

Models 7212, 7214, 7218 may be followed by letter "N", "U" or /2, /6, /12, /17, /19.

Models DV6224, DV6248, DV6424, DV6448 may be followed by two digits, followed by "TD", followed by one digit, followed by "R", followed by "U", followed by three digits, may be followed TD1.

Models 6248N, 6448 may be followed by two digits, followed by "TD", followed by one digit, followed by "R", followed by "U", followed by three digits; Models 6224N, 6424N may be followed by two digits, followed by "TD", may be followed by "H", followed by one digit, followed by "R", followed by "U", followed by three digits; Model 6448/2TDP-378.

Models RL48-19/12, RL48-19/12ML, RL48-19/14, RL48-19/14ML.

Low voltage DC fans, Series 6212, 6324, 6412; Model 6212, 6324 or 6412 may be followed by N, may be followed by /S or /2 through /39, followed by M or H, may be followed by T, A, I, P, F, may be followed by R or U, may be followed by three digit suffix, may be followed by VP1; Series 6224, 6224N or 6424; Model 6212 or 6412 may be followed by N, may be followed by /S or /2 through /39, followed by H, may be followed by T, A, I, P, F, may be followed by R or U, may be followed by three digit suffix, may be followed by VP1; Series 6248 or 6448; Models 6248 or 6448; Model 6312, 6314, 6318 or 6324 may be followed by N, may be followed by /S or /2 through /39, may be followed by T, A, I, P, F, may be followed by R or U, may be followed by three digit suffix, may be followed by VP1.

Models 4112N, 4114N, 4118N followed by one or two digit suffix, followed by HH, H3, H4, H5, H6, H7 or H8, followed by additional suffixes.

VP1 Models 4114N, 4118N followed by one or two digit suffix, followed by HH, H3, H5, H6, H7 or H8, followed by additional suffixes.

Series RLF35-8/12N, Model RLF35-8/12N followed by one or two digit suffix, may be followed by ML, followed by additional suffixes; Series RLF35-8/14N, Model RLF35-8/14N followed by one or two digit suffix, followed by additional suffixes.

Model Series K1G165AA or DV165/14, followed by M or N.

Model Series 6318TDH4, DV6318TDH4, DV6318TDH5.

Model Series 2214, 2218 followed by F/, may be followed by 2 digits, followed by TDH, followed by H (2218 only) or 4, followed by additional suffixes.

Models Series 632N#, 634N#, 632#H, 638#H, 638/2HH, may be followed by T, A, I, P or F, followed by R or U, followed by three additional digits.

Fans, Electric, Model 4412, followed by one or two digit suffix, may be followed by LL, L, M, N, H or HH, followed by additional suffixes.

Model 4414, followed by one or two digit suffix, may be followed by LL, L3, L, M, N, H or HH, followed by additional suffixes.

Model 4416, followed by 2 digits suffix followed by H or M; followed by additional three suffixes.

Model 4418, followed by one or two digit suffix, may be followed by LL, L, N, H or HH, followed by additional suffixes.

Model Series 4412FN, 4412FN, 4412FN and AC 4400 FNN, followed by one or two digit suffix; followed by N or H; followed by additional suffixes.

Model Series 4414FN, followed by one or two digit suffix, followed by N or H, followed by additional suffixes.

Model Series 4418FN, followed by one or two digit suffix, followed by N or H, followed by additional suffixes.

Model AC3200J..H.

Models AC6100NM, AC6100NMU, AC6200NM, AC6400NM.

Model AC6200N.

Model AC8300H.

Series 612J, Model 612J, followed by one or two digit suffix, followed by H, followed by additional suffixes. See Nomenclature Breakdown.

Series 614J, Model 614J, followed by one or two digit suffix, followed by H, followed by additional suffixes. See Nomenclature Breakdown.

Series 618J, Model 618J, followed by one or two digit suffix, followed by H, followed by additional suffixes. See Nomenclature Breakdown.

Models 8212J, 8214J, 8218J, followed by one or two digit suffix, followed by H or H4, followed by additional suffixes. See Nomenclature Breakdown.

Vario Pro Models 8212J, 8214J, 8218J, followed by one or two digit suffix, followed by H or H4, followed by additional suffixes. See Nomenclature Breakdown.

Model RL65-21/12, followed by one or two digit suffix, may be followed by H, followed by additional suffixes. See Nomenclature Breakdown.

Model RL65-21/14, followed by one or two digit suffix, may be followed by H, followed by additional suffixes. See Nomenclature Breakdown.

Models RL65-18/12, RL65-13/12 followed by one or two digit suffix, followed by additional suffixes. See Nomenclature Breakdown.

Models 8212J, 8214J, 8218J, followed by one or two digit suffix; followed by additional suffixes. See Nomenclature Breakdown.

Vario Pro Series, Models 8214, 8218, followed by one or two digit suffix; may be followed by H; followed by additional suffixes. See Nomenclature Breakdown.

Model ACi 4410 HH.

DC fan racks, Models 9975414118, 9975414130 through 9975414139, 9975414140 through 9975414149, RER125-19/18N39HT, RER125-19/18N39HTU.

Models 9975414150 through 9975414159.

* Models may be provided with number and/or letter suffixes that denote wire lengths, terminal blocks, speed sensors, etc.; Models may be provided with a letter "E" prefix that denotes the EBM logo.

Marking: Company name or trademark "PAMOTOR", model and type designation and electrical rating; May have prefix letter C.

Last Updated on 2013-05-24

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2013 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2013 UL LLC".