



## Starrett KDC08021RS Deep Cut Bi-Metal Holesaw Kit (612-9602)



### Features

- 10 Pc Deep Cut Bi-Metal Holesaw Kit
- Holesaw Diameters: 20mm, 22mm, 25mm, 29mm, 35mm, 44mm, 68mm, 73mm
- Arbors: A1E (14-30mm), A10E (32mm-210mm)
- 51mm (2") hole saw depth improves cutting performance on tubes, particularly where there is a need to cut through both sides.
- New tooth material with extra cobalt for enhanced heat and wear resistance - improving the product life.
- Ideal for solid materials greater than 3mm (1/8") in thickness.
- Aggressive material penetration and kerf clearance.

### Description

The new Deep Cut Bi-Metal Hole Saws combine the aggressive tooth form from our previous Dual Pitch Hole Saws, with the new extra cobalt HSS teeth to provide enhanced heat and wear resistance. Featuring a 10mm increase in hole-saw depth and aggressive material penetration and kerf clearance, it is the complete multi-purpose hole saw to penetrate deep into metals, wood, plastic, plaster and other materials.

Recommended cutting depth - greater than 3mm (1/8").