

Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit	Minimum load factor	Speed ratings		Mass	Designation
d	D	H	dynamic	static	P_u	A	Reference speed	Limiting speed		
mm			kN	C_0	kN	-	r/min		kg	-
25	42	11	18,2	39	1,43	0,0079	6300	9000	0,060	51105

