



Datasheet

Stock No: 264-7342

ENGLISH

# RS Pro M25 Nickel Plated Brass Cable Gland



## Product Details:

### IP68 Metric Gland

Glands for use with screened cable are designed to connect the screen of the cable to the enclosure screening system. This is achieved by the use of 2 tapered rings applying force onto an endless spring washer against the screen, to ensure a positive contact. Assembly is simple by exposing the screen, applying spring and washers then tightening the brass cable gland assembly. The gland bonds the screen to the housing.

## Features and Benefits

- IP68 protection
- Quick and easy assembly
- Santoprene (polyolefin) rubber seal provides good weather and chemical resistance

**Note:** Not supplied with locknuts.

**Standards:** EN50262

## Specifications:

Thread Size:	M25
Material:	Nickel Plated Brass
Maximum Cable Diameter:	9.5mm
Minimum Cable Diameter:	6mm
IP Rating:	IP68
Minimum Operating Temperature:	-40°C
Maximum Operating Temperature:	+135°C

