

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION .19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC  
DY

DIST  
-

REVISIONS

| P | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|---|-----|---------------------------|---------|-----|------|
|   | D2  | REVISED ECR-09-003866     | 19FEB09 | LYM | LSF  |
|   | D3  | REVISED PER ECO-09-022178 | 24SEP09 | KK  | AEG  |

0.40  
TYP

G

1.0  
TYP

3

KINK CONTACT

tyco

KINK CONTACT

CIRCUIT # 1

3.0

A

B

1.0±0.1

E<sup>+0.2</sup><sub>-0</sub>

H±0.15

SECTION A - A  
(FOR EVEN POSITION CONTACTS)  
SCALE 10:1

1.80  
REF

4.1  
REF

2.30  
REF

5.6

3.0±0.5

2.00

0.50<sup>+0.45</sup><sub>-0.15</sub>

SECTION B - B  
(FOR ODD POSITION CONTACTS)  
SCALE 10:1

NOTES:

1

MATERIAL:  
HOUSING: GLASS FILLED PBT, NATURAL COLOR (WHITE)  
CONTACT: PHOSPHOR BRONZE

2

FINISH: MATTE TIN OVER NICKEL UNDERPLATE

3

KINK CONTACTS LOCATION:  
8P & BELOW: ALL POSITIONS  
9P & ABOVE: 4 CONTACTS (2 PAIRS) EACH END

4

PACKAGING: TUBE

5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

STATUS

| H | G | F | E | POS. | PART NO. |
|---|---|---|---|------|----------|
|   |   |   |   |      | 84984-4  |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING  
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

|        |       |
|--------|-------|
| 0 PLC  | ±0.30 |
| 1 PLC  | ±0.30 |
| 2 PLC  | ±0.30 |
| 3 PLC  | ±     |
| 4 PLC  | ±     |
| ANGLES | ±3°   |

MATERIAL

FINISH

DWN  
WYLEE

CHK  
LP TAN

APVD  
SF LEONG

PRODUCT SPEC  
108-51058

APPLICATION SPEC  
-

WEIGHT  
-

CUSTOMER DRAWING

15JUN04

Tyco Electronics

Singapore Pte. Ltd.

NAME  
ASSY, 1.00mm FFC CONN  
DIP, V

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-84984

SCALE  
5:1

SHEET  
1

OF  
2

REV  
D3

AMP 1470-19 REV 09MAY94

Pro/ENGINEER DRAWING

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

.19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


| LOC | DIST | REVISIONS |     |             |      |          |
|-----|------|-----------|-----|-------------|------|----------|
| DY  | -    | P         | LTR | DESCRIPTION | DATE | DWN APVD |
|     |      |           |     | SEE SHEET 1 |      |          |



RECOMMENDED FFC/FPC



RECOMMENDED PCB LAYOUT (THK= 1.6±0.1)  
(FOR ODD POSITION CONNECTORS)  
NON-ACCUMULATIVE TOLERANCE



RECOMMENDED PCB LAYOUT (THK= 1.6±0.1)  
(FOR EVEN POSITION CONNECTORS)  
NON-ACCUMULATIVE TOLERANCE

|                                                                                                                                                                               |  |                           |                                         |                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------|-----------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. |  | DWN<br>WYLEE<br>15JUN04   | Tyco Electronics<br>Singapore Pte. Ltd. |                    |
| DIMENSIONS:<br>mm                                                                                                                                                             |  | CHK<br>LP TAN             |                                         |                    |
|                                                                                                                                                                               |  | APVD<br>SEIFONG           | NAME<br>ASSY, 1.00mm FFC CONN<br>DIP, V |                    |
|                                                                                                                                                                               |  | PRODUCT SPEC<br>108-51058 |                                         |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                                                                                                        |  | APPLICATION SPEC<br>-     | SIZE<br>A3                              | CAGE CODE<br>00779 |
| MATERIAL<br>                                                                                                                                                                  |  | WEIGHT<br>-               | DRAWING NO<br>C=84984                   |                    |
| FINISH<br>                                                                                                                                                                    |  | CUSTOMER DRAWING          | SCALE<br>5:1                            | SHEET<br>2 OF 2    |
|                                                                                                                                                                               |  |                           | REV<br>D3                               |                    |