



LED Floodlights – J5 Range



Description

This range of LED Slimline Floodlights is ideal for domestic and commercial applications, and offer significant energy savings over traditional tungsten halogen fittings. Suitable for garden lighting, car park area lighting, security lighting, sports areas and amenity lighting.

Features

- Tilt and pan adjustable heads
- Single and twin head options
- Energy efficient replacement for tungsten halogen fittings
- Available with PIR with built in dusk to dawn sensor
- Integral driver
- 25,000 hours rated life
- 3 year guarantee

Range

10W LED Floodlight – Non PIR	7884647
10W LED Floodlight – PIR	7884640
20W LED Floodlight – Non PIR	7884644
20W LED Floodlight – PIR	7884653

Dimensions, Beam Angle & Lumens

	Lumens	Fitting Dimensions (L x W x D)
7884647	720	206 x 90 x 60
7884640	720	238 x 90 x 80
7884644	1440	206 x 198 x 60
7884653	1440	238 x 198 x 80

Technical Specification

Voltage	230V ~
Driver	Integral
Lamp col. temp.	6400K
PIR detection angle	140°
PIR detection range	8-10m
Timer	10s – 10min
Lux level	2 – 200 lux
IP Rating	IP54

Standards

- BS EN 60598-1+A11
- BS EN 60598-2-5
- BS EN 61347-1
- BS EN 61347-2-13
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3