


Datasheet

FLUSH-MOUNTING SOCKET 6P+E IP66/IP67






TechData	
Rated current	16A
Commercial series	OPTIMA-SEVEN Series
Poles	6P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	50Hz
Working frequency	60Hz
Colour	RED
Syntetical description	FLUSH-MOUNTING SOCKET
Protection degree	IP66/IP67
Types of available outlets	STRAIGHT

Approvals and Certifications



Standards and Laws

-  EN 60309-1 (1999)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

Packaging

Description	Box
Quantity	10
Gross weight	2.29 KG
Volume	8436 CCM
Dimensions	185x285x160 (MM)