

Datasheet

3way Iso 16 input AA converter 24-240V

RS Stock number 794-8527



Microcompact Analogue/Analogue Converters

DIN rail mounting Microcompact analogue/analogue converters for industrial applications.

3-way isolation

LED indicator

Screw/spring terminals

IP 20 protection

Input Range	0 → 1 V, 0 → 10 mA, 0 → 10 V, 0 → 100 mV, 0 → 2 V, 0 → 20 mA, 0 → 20 V, 0 → 300 mV, 0 → 5 mA, 0 → 5 V, 0 → 500 mV, 0 → 60 mV, ±20 mA, ±5 mA, 2 to 10 V, 4 → 20 mA
Input Type	Analogue
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-25°C
Mounting Type	DIN Rail
Operating Temperature Range	-25 → +60 °C
Output Range	0 → 10 V, 0 → 20 mA, 4 → 20 mA
Output Type	Analogue
Signal Conditioner Type	Isolation
Supply Voltage	16.8 → 30 V dc, 19.2 → 28.8 V ac