



ENGLISH

Datasheet

Nitrile Rubber O-Ring Cord, 1.78mm Diameter, 8.5m Long

RS Stock number 683-0762



Description:

Nitrile O-Ring Cord

Replacement Nitrile® O-Ring cord for fast, on the spot production of O-Rings. Available in diameters between 1.6mm and 8.4mm.

Nitrile is suitable for use within applications running at a maximum continuous temperature of 120°C (or up to 150°C intermittently). Use below -30°C requires special consideration.

Specifications

Diameter:	1.78mm
Length:	8.5m
Material:	Nitrile Rubber