


Product

AK 56



Entries

Entries top end:

17 x M20

2 x M20/M25

1 x M32/M40

Entries bottom end:

15 x M20

2 x M20/M25

1 x M32/M40

Entries on each side:

20 x M20

5 x M25/M32

Distribution board, 4 row, 56 modules, 150 mm rail spacing, screwless PE/N terminal rails each with 6 screwable clamping points, 2.5 - 16 mm², 21 screwless clamping points 1.5 mm² - 4 mm², elastic entries on top, with cable covering, masking and labelling strips, additional double-membrane seals and other accessories

Article: AK 56

Technical Data

Dimensions:

Width: 300 mm

Length: 750 mm

Height: 142 mm

material:

Base: Polystyrene, grey, similar to RAL 7035

Cover: Polystyrene, grey, similar to RAL 7035

Hinged window: Polycarbonat, transparent

Sealing: Polyurethane

Cover screw: Polyamide 6, fiber-glass reinforced

Properties:

Number of distribution units:	56
Tackable:	√
Fire protection:	none
Halogen-free:	√
Heavy metals-free:	√
PVC-free:	√
Silicone-free:	√
