




- ① NYLON, UL 94-VO RATED, RED.
- ② PHOSPHOR BRONZE.
- ③ 3.81um [.000150] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- ④ 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- ⑤ 3.81um [.000150] MIN TIN OVER 1.27um [.000050] MIN NICKEL.
- ⑥ 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

		NO	1-207526-0
		YES	207526-9
		NO	207526-8
		YES	207526-7
		NO	207526-4
		YES	207526-3
		NO	207526-2
		YES	207526-1
CONTACT FINISH		MOUNTING TABS	PART NO

DOCUMENT.	DWN	03/20/92			TE Connectivity			
	L.SIPE							
DIMENSIONS UNLESS SPECIFIED:	CHK	3-25-92	NAME SOCKET HEADER ASSEMBLY, 9 POSITION, METRIMATE					
	R.STONE							
	APVD	-						
	PRODUCT SPEC							
	108-10033							
-	APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO					
-	-							
0.25 [.010]	-							
- ± -	-							
SEE TABLE	WEIGHT	-	A2	00779	C=207526	-		
CUSTOMER DRAWING			SCALE	4:1	SHEET	1 of 1	REV	M1