

# QOU120

## MINIATURE CIRCUIT BREAKER 120/240V 20A



Download your QOU120 datasheet



[Characteristics](#) | Documents & Downloads

### Main Hide

<b>Product or component type</b>	Miniature circuit-breaker
<b>Range of product</b>	QOU
<b>Circuit breaker type</b>	Standard
<b>[In] rated current</b>	20 A
<b>Poles description</b>	1P
<b>Short-circuit current</b>	10 kA
<b>Electrical connection</b>	Slotted box lugs (line and load)
<b>Circuit breaker application</b>	HACR and Switching Duty rated
<b>Accessory / separate part type</b>	None
<b>Product certifications</b>	CSA IEC UL listed
<b>[Ue] rated operational voltage</b>	120/240 V AC
<b>Mounting mode</b>	Unit mount
<b>AWG gauge</b>	AWG 14...AWG 2 (aluminium/copper)

### Offer Sustainability Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 1323 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty Hide

<b>Period</b>	18 months
---------------	-----------