

General Information

| | |
|------------------------|--|
| Extended Product Type: | MB6/8.L8 |
| Product ID: | 1SNA115418R1600 |
| EAN: | 3472591154184 |
| Catalog Description: | MB6/8.L8 Distribution Terminal Blocks |
| Long Description: | MB6/8.L8 Distribution Terminal Blocks - Grey, 6mm ² Rated Cross Section, 66.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail |

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

Ordering

| | |
|-------------------------|---------------|
| EAN: | 3472591154184 |
| Minimum Order Quantity: | 1 piece |
| Customs Tariff Number: | 85369010 |

Dimensions

| | |
|---------------------|---------|
| Product Net Width: | 66.5 mm |
| Product Net Height: | 44.5 mm |
| Product Net Depth: | 40.5 mm |
| Product Net Weight: | 102 g |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 50 mm |
| Package Level 1 Height: | 49 mm |
| Package Level 1 Length: | 133 mm |
| Package Level 1 Gross Weight: | 0.102 kg |
| Package Level 1 EAN: | 3472591154184 |
| Package Level 2 Units: | 30 piece |
| Package Level 2 Width: | 300 mm |
| Package Level 2 Height: | 150 mm |
| Package Level 2 Length: | 500 mm |
| Package Level 2 Gross Weight: | 3.35 kg |
| Package Level 3 Units: | 1440 piece |
| Product Packing Type: | Box |

Environmental

| | |
|--------------|---|
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|--------------|---|

Technical UL/CSA

| | |
|---------------------------------|----|
| Flammability According to UL94: | V2 |
|---------------------------------|----|

Additional Information

| | |
|--|--|
| Color: | grey |
| Connection Type: | Screw clamp |
| Function: | Distribution |
| IIT Publishing Status: | Level 0 - Information enabled |
| Mounting on DIN Rail: | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Number of Levels: | 1 |
| Pollution Degree: | 2 |
| Product Main Type: | MB6/8 |
| Product Name: | Terminal Block |
| Rated Cross-Section: | 6 mm ² |
| Rated Impulse Withstand Voltage (U _{imp}): | 8 kV |
| Recommended Screw Driver: | 4 mm |
| Spacing: | 8 mm |
| Sub-Function: | Phases |
| Tightening Torque: | acc. IEC 60947-1 0.8 N·m Manufacturer 1 N·m |
| Wire Stripping Length: | 12 mm |

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: 1SNC160001C0207-CH-G Distribution terminals

Declaration of Conformity - CE: 1SND225024C1005

EAC Certificate: 1SND161009A1100

RoHS Information: 1SND230023F0202

Classifications

ETIM 4.0: EC001894 - Distributor assembly terminal blocks

ETIM 5.0: EC001894 - Distributor assembly terminal blocks

Object Classification Code: X

