

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Application	Voice & Data Communication
Approval/Compliance	UL Recognised;CSA Accepted;Halogen Free (DIN VDE 0472/part 815)
Article No.	114706
Brady Material No.	B-425
Material Type	Polypropylene
Brand	WorkHorse™ Series
Colour	White
Finish	Matt
Description	Flags for the BMP™71 Label Printer.
Max. Characters per Line	29
Max. Lines of Text	4
Max. Service Temp. °C	80
Order Reference	M71FT-1-425
Printable Area - Height (mm)	10.00
Printer Compatibility	BMP71
Ribbon Series	M71-R4300
Shape	Rectangle
Size - Height (mm)	20.00
Size - Width (mm)	30.00
Additional Information	Excellent solvent resistance
Total Qty per Pack	250 Label(s) / Box
Vertical Repeat (mm)	43.56
Voice/Data Application	Fibre Optic Labels/Flags

Industry	Data & Telecommunications;Electrical
Min. Service Temp. °C	-70
Printable Area - Width (mm)	30.00
QTY. per Row	1
Thickness (mm)	0.1143