

TONO



APPLICATIONS

Appliances and furniture on mats, carpet and interior surfaces.

CASTOR ASSEMBLY: • Pressed steel. • Plate, central bolt-hole or threaded stem fitting. • Bright chrome-plated protection or black epoxy paint.

SWIVEL: • Swivel on two rows of balls.

WHEEL: • Spherical with wide grey (chrome finish) or black (black finish) thermoplastic rubber section.

HUB: • Plain bore. • Riveted axle.

TONO with plate

| | | | | | | | Type | | | Code | Code | EAN 13 | |
|----|----|----|-------|-------|---|----|------|--|-------|--------|-------------|---------|-----------------|
| 40 | 40 | 62 | 42x42 | 28x28 | 4 | 40 | | | 0,160 | Chrome | 17 410 0000 | 3 63376 | 339680 717410 3 |
| | | | | | | | | | 0,160 | Black | 17 411 0000 | | 339680 717411 0 |
| 50 | 50 | 72 | 47x47 | 34x34 | 6 | 45 | | | 0,230 | Chrome | 17 510 0000 | 3 63476 | 339680 717510 0 |
| | | | | | | | | | 0,230 | Black | 17 511 0000 | | 339680 717511 7 |

TONO with bolt-hole

| | | | | | | Type | | | Code | Code | EAN 13 |
|----|----|----|----|----|--|------|-------|--------|-------------|---------|-----------------|
| 40 | 40 | 58 | 10 | 40 | | | 0,130 | Chrome | 17 400 0000 | 3 13376 | 339680 717400 4 |
| | | | | | | | 0,130 | Black | 17 401 0000 | | 339680 717401 1 |
| 50 | 50 | 70 | 10 | 45 | | | 0,180 | Chrome | 17 500 0000 | 3 13476 | 339680 717500 1 |
| | | | | | | | 0,180 | Black | 17 501 0000 | | 339680 717501 8 |

TONO with threaded stem

| | | | | | | Type | | | Code | Code | EAN 13 | |
|----|----|----|-----|----|----|------|--|-------|--------|-------------|---------|-----------------|
| 40 | 40 | 65 | M8 | 20 | 40 | | | 0,150 | Chrome | 17 409 0000 | 3 43376 | 339680 717409 7 |
| | | | | | | | | 0,150 | Black | 17 410 0000 | | 339680 717410 4 |
| 50 | 50 | 75 | M10 | 20 | 45 | | | 0,210 | Chrome | 17 509 0000 | 3 43476 | 339680 717509 4 |
| | | | | | | | | 0,210 | Black | 17 510 0000 | | 339680 717510 1 |

