



LOGO! 24CEO, LOGIC MODULE, WITHOUT DISPLAY, PU/I/O:
 24V/24V/24V TRANS., 8 DI (4AI)/4 DO; MEM 400 BLOCKS
 EXPANDABLE, ETHERNET BIULD IN WEB-SERVER, DATALOG
 STANDARD MICRO SD CARD FOR LOGO! SOFT COMFORT V8
 PREVIOS PROJECT USABEL

Installation type/mounting

Mounting on 35 mm DIN rail, 4 spacing units wide

Supply voltage

Rated value (DC)	Yes
• 24 V DC	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Time of day

Time switching clocks	
• Number	190
• Power reserve	480 h

Digital inputs

Number of digital inputs 8; Of which 4 can be used in analog mode (0 to 10 V)

Digital outputs

Number of digital outputs	4; Transistor
short-circuit protection	Yes; electrical (1 A)

Output current

• for signal "1" permissible range for 0 to 55 °C, max.	0.3 A
---	-------

EMC

Emission of radio interference acc. to EN 55 011

• Limit class B, for use in residential areas	Yes; Radio interference suppression according to EN55011, Limit Value Class B
---	---

Degree and class of protection	
Degree of protection to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
Developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Dimensions	
Width	71.5 mm
Height	90 mm
Depth	58 mm
last modified:	20.04.2015