

Datasheet

RS Pro Toggle Switch DPDT On-On, 0.4 A@ 20 V, Panel Mount

RS Stock No: **317-588**



Product Details

RS Pro DPDT toggle switch has a locking lever that retains one switch position to prevent accidental switching. This panel mount switch performs on-on operation. It withstands currents up to 0.4 A at 20 V voltage. The copper alloy contacts offer superior performance.

Features and Benefits

- Switches with a locking lever
- Silver contacts
- Glass filled polyester case

Specifications:

Actuator Length	10.5 mm
Actuator Material	Chrome Plated Brass
Contact Configuration	DPDT
Contact Current Rating	0.4 VA at 20 V ac/dc
Contact Material	Gold Plated Copper Alloy
Contact Resistance	10 mΩ
Maximum Operating Temperature	+70°C
Mechanical Life	50000 to 100000 cycles
Minimum Operating Temperature	-20°C
Mounting Type	Panel Mount
Operating Temperature Range	-20 to +70°C
Panel Cut Out Diameter	6.2 mm
Standards Met	CSA Recognised, RoHS Compliant, UL 94V-0 Listed
Switch Operation	On-On
Terminal Type	Solder
Actuator Type	Locking Lever
Bushing Style	Threaded