



The Symphoni is an extremely efficient wall siren well suited for large installations where ultra-low current is critical. There is a standard version, providing UK alarm tones and an "E" version that has tones including the German DIN tone and the Netherlands Slow Whoop.

An IP66 rated WP version is also available.


Features

- Low 5mA current consumption
- 100dB(A)
- Automatic synchronisation
- Weatherproof option

Benefits

- Maximises the number of devices on a system
- Certified for Fire use
- Improved tone clarity, reducing confusion
- Suitable for outdoor use


Dimensions



Technical Specification

Voltage	18 - 30Vdc
Current	5mA
Sound Output	100dB(A)
Tones	3
Volume Control	10dB
Monitoring	Reverse polarity
Temperature	- 10°C to + 55°C - 25°C to + 70°C (WP)
Protection	IP21C, IP66 (WP)
Construction	ABS
Weight	0.21Kg, 0.32Kg (WP)
Colours	Red or white

WP version white



Catalogue Numbers

Reference	Cat No	Description
SY/R	650001FULL-0003X	Symphoni Sounder Red
SY/W1	650002FULL-0004X	Symphoni Sounder White
SY/R/E	650008FULL-0073X	Symphoni Sounder, Red, European tone version
SY/W1/E	650009FULL-0074X	Symphoni Sounder, Signal White, European tone version
SY/IP/W	654036FULL-0225X	Symphoni Sounder, White, WP IP66