

## 10.8V KIT



**Part Number: 0601 858 043**

**Barcode: 3 165 140 594 486**

### **Includes:**

1x GDR 10.8Li Impact Driver  
1X GOP 10.8V-Li Multi-Cutter  
1x GSR 10.8-2Li Drill Driver  
2x 1.3Ah 10.8V Li-Ion Batteries  
1x 30min Charger

### **Specifications**

#### **GOP 10.8V-LI**

|                       |                    |
|-----------------------|--------------------|
| No-load speed         | 5.000 – 20.000 rpm |
| Oscillation angle L/R | 1.4 °              |
| LxH                   | 280x95 mm          |

#### **GDR10.8-LI**

|               |            |
|---------------|------------|
| No load speed | 0-2600 rpm |
| Impact rate   | 0-3100 bpm |
| Max Torque    | 105 Nm     |
| Weight        | 0.96 kg    |

#### **GSR 10.8-2LI**

|                                                   |               |
|---------------------------------------------------|---------------|
| No-load speed (1 <sup>st</sup> /2 <sup>nd</sup> ) | 0-350/1300rpm |
| Torque Hard/soft :                                | 30/13 Nm      |
| Drilling dia. in wood/steel                       | 19/10 mm      |
| Weight                                            | 0.95kg        |



**BOSCH**

## GBH 18V-Li BB



### Specifications:

|                                |                |
|--------------------------------|----------------|
| Rated voltage                  | 18 V           |
| Capacity                       | 1.3/2.6/3.0 Ah |
| Impact energy                  | 0-1.7 J        |
| Impact rate                    | 4,450 bpm      |
| Weight incl, battery           | 2.6 kg         |
| Max. drilling dia. in concrete | 18mm           |
| Max. drilling dia in steel     | 13mm           |
| Max. drilling dia in wood      | 30mm           |

### Features and Benefits:

- Innovative brushless motor (Electronically Commutated)
- Compact body (DIN A4 size) and light weight (2.6kg) for easy handling
- Pneumatic hammer mechanism, for high performance with compact sizes 2-mode drive for hammer drilling and wood metal drilling
- Unbeatable runtime – 115 holes (6x 40mm) in concrete with one battery charge (with 3.0Ah) by EC motor
- Electronic Cell Protection (ECP) and Electronic Motor Protection (EMP)
- The best balance rotary hammer in the 18 V class 0 Size, Speed, Power and Runtime
- Includes L-BOXX 136 carry case

**Part Number: 0611904300**

**Barcode: 3165140571623**



**BOSCH**

## GDR 18V-Li Barebones



### Technical Specifications

|                          |              |
|--------------------------|--------------|
| Battery voltage          | 18V-Li       |
| Battery capacity         | 1,3 Ah       |
| Weight incl. battery     | 1.5 kg       |
| Charging time, approx.   | 45 min       |
| No Load speed            | 0 – 2800 rpm |
| Torque hard applications | 160 Nm       |
| Rated impact rate        | 0 – 3200 rpm |

### Features & Benefits:

- The first 18-volt impact driver with flexible battery system
- High torque and high impact rate (3,200 bpm) for fast work progress when driving screws in metal (up to M 14) and wood
- Very short design for perfect handling, even in the tightest spaces and overhead
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and total discharge
- Extremely robust: due to flexible Dura Shield housing
- Practical battery charge level indicator constantly shows how much energy is left in the battery

**Part Number: 0601 9A1 341**

**Barcode: 3 165 140 537 087**



**BOSCH**

## GDS 18 V-LI HT BAREBONES



### Specification :

|                            |            |
|----------------------------|------------|
| Voltage                    | 18 V       |
| Battery technology :       | Li-Ion     |
| Battery capacity max. :    | 3.0Ah      |
| Square drive size :        | 1/2"       |
| Max. torque :              | 650 Nm     |
| No load speed :            | 0–1900 rpm |
| Impact rate :              | 0–2100 bpm |
| Weight including battery : | 3.0 kg     |

### Features & Benefits:

- ▶ Highest torque (650 Nm) in its class for the toughest screw diving applications in metal (M12-M20) and concrete
- ▶ Extremely robust and tough due to all-metal gearbox and metal housing
- ▶ At 3.0 kg it is one of the lightest “High-Torque” impact wrenches
- ▶ Unique Bosch Premium lithium-ion technology for unbeatable battery runtime
- ▶ Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and total discharge
- ▶ Practical battery charge level indicator constantly shows how much energy is left in the battery

**Part Number: 0601 9B1 300**

**Barcode: 3 165 140 572 003**



**BOSCH**

## GLI 18V-LI VariLED BAREBONES



### Specification :

|                 |         |
|-----------------|---------|
| Bulb type       | LED     |
| Voltage         | 14.4/18 |
| Brightness (lx) | 300     |
| Weight (kg)     | 0.3     |

### Features & Benefits:

- The brightest pocket-sized work light (300 lux) in its class due to 3 innovative Power LEDs.
- Very compact due to innovative folding mechanism
- Versatile range of applications due to adjustable light beam (spot/flood) and 9 settable lighting angles
- For flexible use with all Bosch 14.4 and 18 volt lithium-ion batteries
- Practical hard rubber strap for fixing the worklight to enable targeted illumination of the work area

**Part Number: 0601443400**

**Barcode: 3165140600422**



**BOSCH**

## GOP 250 CE



### Technical specifications

|                                 |                |
|---------------------------------|----------------|
| Rated power                     | 250W           |
| No load speed rate (opm)        | 8000-20000 opm |
| Oscillation angle on left/right | 1.4 degrees    |

### Features and Benefits

- Powerful 250W motor with constant electronics for consistent work progress for any application
- Small grip circumference for convenient, comfortable work and precise results
- Ball socket joint and Zn gear box, for flexibility, robustness and vibration reduction
- Easy service access for fast change of carbon brushes
- Robust AC holder, easy to change AC with standard hex key
- Attached AC adaptor for adapting of Fein accessories (SDS)
- 6 speed dial wheel, appropriate for the material
- Ball socket joint to avoid current leakage
- Constant electronics

**Part Number: 0601230040**

**Barcode: 3165140596589**



**BOSCH**

## GOS 10.8 V-LI BB



### Technical specifications

|                                 |                |
|---------------------------------|----------------|
| Voltage                         | 10.8V          |
| Display Size                    | 68.6mm         |
| Display resolution              | 320x240px      |
| Diameter of camera head         | 17mm           |
| Length of camera cable          | 122cm          |
| Number of LED lighting stages   | 9              |
| Runtime with one battery charge | up to 15 hours |

### Features and benefits

- Bright power-LED for optimum illumination in dark areas
- Extra-long waterproof camera cable with compact camera head

**Part Number: 0601241004**

**Barcode: 3165140621014**

## GOS 10.8V-Li



### Technical Specifications

|                                 |              |
|---------------------------------|--------------|
| Battery voltage                 | 10,8 V       |
| Display size                    | 68.6 mm      |
| Display resolution              | 320 x 240 px |
| Diameter of camera head         | 17 mm        |
| Length of camera cable          | 122 cm       |
| Number of LED lighting stages   | 9            |
| Runtime with one battery charge | up to 15 h   |

### Features and Benefits

- Best optics with the 68.6mm high resolution display including realistic colour reproduction, depth of field, dirty lens performance, field of view and usable range
- Bright Power-LED with nine brightness levels for optimum illumination in dark areas
- Extra-long, waterproof camera cable (122 cm) with small camera head for a flexible range of applications
- Video-out interface for external image transfer
- Bosch Premium lithium-ion technology for longer lifetime

**Part Number: 0601241040**

**Barcode: 3165140651967**

## GSA 10.8V-Li



### Technical Specifications

|                         |                   |
|-------------------------|-------------------|
| Battery voltage         | 10,8 V            |
| No-load speed           | 0 – 3000 rpm      |
| Stroke lengths          | 14.5 mm           |
| Tool dimensions (L/H/W) | 268 x 132 x 60 mm |
| Weight                  | 1.2 kg            |

### Features and Benefits

- The most compact design in its class for perfect handling and versatile applications in wood, metal and plastic.
- Excellent ergonomics: small grip circumference and lightweight (only 1.2kg) for maximum comfort
- Practical battery charge level indicator constantly shows how much energy is left in the battery
- Bosch SDS system for fast and convenient saw blade changes
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and deep discharge
- Integrated LED light for illuminating the work area

**Part Number 060164L902**

**Bar Code: 3165140603836**



**BOSCH**

## GSB 10.8-2-Li



### Specifications:

|                                       |            |
|---------------------------------------|------------|
| Voltage (V)/Capacity (Ah)             | 10.8/1.3   |
| Batteries/Charger                     | 2/30 min   |
| No load speed 1st/2nd (rpm)           | 0-380/1300 |
| Impact rate (bpm)                     | 0-19,500   |
| Max drilling diameter wood/steel (mm) | 19/10      |
| Torque setting range                  | 20+1       |
| Max torque hard/soft (Nm)             | 30/13      |
| Weight (kg)                           | 1.0        |

### Features and Benefits:

- Professional performance: newly developed 2-speed gearbox for powerful screw driving and drilling applications in wood with metal and impact drilling in masonry
- Bright Power-LED for optimum illumination in dark areas
- Most compact: shortest design (187mm) in its class for optimum handling, especially when performing drilling and screw driving applications overhead and in tight spaces
- Lowest weight: only 1.0 kg for perfect handling and low fatigue working

**Part Number: 0615990FC5**

**Barcode: 3165140743921**



**BOSCH**

## GSB 19-2RE



### Technical Specifications:

|                                         |                       |
|-----------------------------------------|-----------------------|
| Rated power input                       | 850 W                 |
| No load speed                           | 0 - 1.000 / 3.000 rpm |
| Weight without cable                    | 2.7kg                 |
| Torque (soft screw driving application) | 38,6 / 13,8 Nm        |
| Rated torque                            | 3,6 / 15,5 Nm         |
| Impact rate                             | 0-17000/51000 rpm     |
| Max drilling dia. in Steel              | 13/8 mm               |
| Max drilling dia. in Wood               | 40/25 mm              |
| Max drilling dia. In Stone              | 20/15 mm              |
| Max drilling dia. In Concrete           | 18/13 mm              |

### Features and Benefits:

- The most versatile bundle of power in its class
- Versatility for high torque or high speed applications
- 2 gear, 850W of pure power, high torque: 36/15.5 Nm
- Fastest drilling in its class
- High durability due to metal gear housing, ball grommet, double fan motor and stacked construction
- Mechanical Overload clutch; Anti rotation system increases safety while working
- Innovative auxiliary side handle due to new axial security
- Rotatable brush plate means extreme dust resistance, same power in forward and reverse

**Part Number: 0601 17B 640**

**Barcode: 3 165 140 569 316**



**BOSCH**

## GSB 21-2RE KC



**Part Number: 060119C640**

**Barcode: 3165140519618**

### Technical Specifications:

|                                         |                      |
|-----------------------------------------|----------------------|
| Rated power input                       | 1100 W               |
| No load speed                           | 0 - 9000 / 3.000 rpm |
| Weight without cable                    | 2.8kg                |
| Torque (soft screw driving application) | 40 / 15 Nm           |
| Impact rate                             | 0-15300/51000 rpm    |
| Max drilling dia. in Steel              | 16/8 mm              |
| Max drilling dia. in Wood               | 40/25 mm             |
| Max drilling dia. In Concrete           | 22/13 mm             |

### Features and Benefits:

- High torque for the most heavy-duty applications with large diameters (drilling, working with core cutters and hole saws), screw driving and stirring
- Sturdy metal gear housing for long lifetime
- Anti-rotation mechanical overload clutch for high level of work safety
- New safety handle with innovative attachment and soft grip for a secure hold on the tool
- Rotating brush plate for constant power in reverse and forward rotation
- Speed pre-selection with setting wheel for precise work

## GSB18V-LI Striker II 1.3Ah



**Part Number: F005XR0135**

**Barcode: 3165140590389**

### Specifications

|                                      |             |
|--------------------------------------|-------------|
| Battery Voltage (V)                  | 18          |
| Battery Capacity                     | 1.3Ah       |
| Torque settings                      | 18+1        |
| Torque Soft/Hard (Nm)                | 23/60       |
| Max. impact rate (bpm)               | 25,500      |
| Chuck size, min./max.(mm)            | 1.5/13      |
| No Load Speed (rpm)                  | 0-500/1,700 |
| Max. drilling dia in wood/steel (mm) | 32/13       |
| Max. screw diameter (mm)             | 8           |
| Weight incl. Battery                 | 1,6 kg      |

### Features and benefits

Shortest head length in its class

- Easy handling even in tight space

Best runtime in its class

- Finish many applications in one charge

Integrated impact function for drilling applications in masonry up to 13mm

- Electronic Motor Protection
- Very short design ergonomically shaped handle – ideal for applications overhead and in tight spaces
- Bosch Electronic Cell Protection (ECP)
- Integrated LED light and practical belt clip keeps the tool within reach at all times



**BOSCH**

## GSB18V-LI Striker II 3.0Ah



**Part Number: F005XR0136**

**Barcode: 9311831507547**

### Specifications

|                                      |             |
|--------------------------------------|-------------|
| Battery Voltage (V)                  | 18          |
| Battery Capacity                     | 3.0Ah       |
| Torque settings                      | 18+1        |
| Torque Soft/Hard (Nm)                | 23/60       |
| Max. impact rate (bpm)               | 25,500      |
| Chuck size, min./max.(mm)            | 1.5/13      |
| No Load Speed (rpm)                  | 0-500/1,700 |
| Max. drilling dia in wood/steel (mm) | 32/13       |
| Max. screw diameter (mm)             | 8           |
| Weight incl. Battery                 | 1,6 kg      |

### Features and benefits

Shortest head length in its class

- Easy handling even in tight space

Best runtime in its class

- Finish many applications in one charge

Integrated impact function for drilling applications in masonry up to 13mm

- Electronic Motor Protection
- Very short design ergonomically shaped handle – ideal for applications overhead and in tight spaces
- Bosch Electronic Cell Protection (ECP)
- Integrated LED light and practical belt clip keeps the tool within reach at all times



**BOSCH**

## GWB 10.8V-Li BB



### Specifications:

|                              |           |
|------------------------------|-----------|
| Battery voltage              | 10.8V     |
| No load speed                | 0-1300rpm |
| Max torque                   | 11Nm      |
| Max. Screw diameter          | 6mm       |
| Max. Drilling dia. For steel | 10mm      |
| Max. Drilling dia. For wood  | 10mm      |
| Electronic clutch            | No        |
| LED lights                   | Yes       |
| Charging time                | 30 min    |

### Features and Benefits:

- Soft grip: optimised handle for a secure grip
- 10mm Keyless chuck
- Variable speed trigger
- Electronic Cell Protection
- Fuel gauge for easier battery management

**Part Number: 0601390905**

**Barcode: 3165140645140**



**BOSCH**

## GWS 18V-Li BB



### Technical specifications

|                                 |          |
|---------------------------------|----------|
| Voltage                         | 18V      |
| No load speed                   | 10000rpm |
| Roughing/cutting disc, diameter | 115mm    |

### Features and Benefits

- Slim grip allows for greater control when grinding and cutting
- Ideal for cuts in tight spaces thanks its compact size
- Soft start and restart protection for increased safety
- Bullet proof guard for protection against shattered discs
- 2 stage switch to avoid unintentional powering of the tool
- 4 pole motor design combined with rare earth magnets for increased power and efficiency
- 4 brush motor significantly increases service life
- Bosch Electronic Cell Protection (ECP) protects the battery against overload, overheating and total discharge

**Part Number: 060193A300**

**Barcode: 3165140557023**



**BOSCH**

## GWS 7-100



### Technical Specifications:

|                    |            |
|--------------------|------------|
| Disc Diameter      | 100mm      |
| Wattage:           | 720W       |
| No Load Speed      | 11,000 RPM |
| Nett Weight        | 1.5kg      |
| Grip Circumference | 176mm      |
| Burst Proof Guard  | Yes        |
| Deadman Switch     | Yes        |

### Features and Benefits:

- Smallest grip circumference of 176mm
- Dimple housing surface for anti-slip
- Strong and tough 720W motor
- Spindle lock for quick disc change
- Small gear head to reach narrow areas
- Burst proof guard for maximum safety to users
- Two-motion switch for one-hand operation and maximum safety to users
- Side and back air inlets for optimal air flow and cooling
- Includes 3 x Grinding Discs

**Part Number: 0601 388 040**

**Barcode: 3 165 140 492 133**



**BOSCH**

## GWS 7-125



### Technical Specifications:

|                      |            |
|----------------------|------------|
| Rated power input    | 720 W      |
| No-load speed        | 11.000 rpm |
| Disc diameter        | 125 mm     |
| Grip circumference   | 176 mm     |
| Weight without cable | 1,5kg      |
| Dead man switch      | Yes        |
| Burst proof guard    | Yes        |

### Features and Benefits

- Smallest grip circumference of 176mm
- Dimple housing surface for anti-slip
- Strong and tough 720W motor
- Spindle lock for quick disc change
- Small gear head to reach narrow areas
- Burst proof guard for maximum safety to users
- Two-motion switch for one-hand operation and maximum safety to users
- Side and back air inlets for optimal air flow and cooling
- Comes in case with 3 x grinding discs

**Part Number: 0601 388 042**

**Barcode: 3 165 140 523 479**



**BOSCH**