

# LAD4TBDL

## CONTACTOR BI DIRECTIONAL LIMITING DIODE



Download your LAD4TBDL datasheet

[Characteristics](#) | Documents & Downloads

### Main Hide

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1D09...D38 LC1DT20...DT40

### Complementary Hide

Mounting location	Side
Mounting mode	By clips
Suppressor technology	Bidirectional peak limiting diode
Control circuit voltage	24 V DC
Maximum peak voltage	2 Uc
Product weight	0.012 kg

### Environment Hide

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Contractual warranty Hide

Period	18 months
--------	-----------