

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Hole saws
Catalogue number	240
Date	19/10/2009


Range Description

A range of Professional quality Bi-metal hole saws, arbors and kits

Features

- Professional quality High Speed Steel Bi-metal holesaws for performance and a long life
- Vari-pitch teeth for fast clean cutting
- Perfect for cutting clean holes in soft and hard wood, plywood, chipboard, steel, stainless steel, Die cast metals, nail embedded wood, plastics etc.





Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
300002	Empty Hole saw display stand		73262080	1
303001	Backing card for display stand 300002		44219098	1
424001	Hole saw 16mm (5/8")	5051074240019	82075060	10
424002	Hole saw 19mm (3/4")	5051074240026	82075060	10
424003	Hole saw 20mm (25/32")	5051074240033	82075060	10
424005	Hole saw 22mm (7/8")	5051074240057	82075060	10
424006	Hole saw 25mm (1")	5051074240064	82075060	10
424007	Hole saw 29mm (1.1/8")	5051074240071	82075060	10
424008	Hole saw 32mm (1.1/4")	5051074240088	82075060	10
424010	Hole saw 38mm (1.1/2")	5051074240101	82075060	10
424011	Hole saw 40mm (1.9/16")	5051074240118	82075060	10
424012	Hole saw 41mm (1.5/8")	5051074240125	82075060	10
424013	Hole saw 43mm (1.11/16")	5051074240132	82075060	10
424014	Hole saw 44mm (1.3/4")	5051074240149	82075060	10
424015	Hole saw 48mm (1.7/8")	5051074240156	82075060	10
424016	Hole saw 51mm (2")	5051074240163	82075060	10
424017	Hole saw 54mm (2.1/8")	5051074240170	82075060	10
424018	Hole saw 57mm (2.1/4")	5051074240187	82075060	10
424019	Hole saw 60mm (2.3/8")	5051074240194	82075060	10
424020	Hole saw 64mm (2.1/2")	5051074240200	82075060	10
424021	Hole saw 65mm (2.9/16")	5051074240217	82075060	10
424022	Hole saw 67mm (2.5/8")	5051074240224	82075060	10
424024	Hole saw 70mm (2.3/4")	5051074240248	82075060	10
424025	Hole saw 73mm (2.7/8")	5051074240255	82075060	10
424026	Hole saw 76mm (3")	5051074240262	82075060	10
424027	Hole saw 79mm (3.1/8")	5051074240279	82075060	10
424028	Hole saw 83mm (3.1/4")	5051074240286	82075060	10
424029	Hole saw 86mm (3.3/8")	5051074240293	82075060	10
424030	Hole saw 89mm (3.1/2")	5051074240309	82075060	10

424031	Hole saw 92mm (3.5/8")	5051074240316	82075060	10
424032	Hole saw 95mm (3.3/4")	5051074240323	82075060	10
424033	Hole saw 102mm (4")	5051074240330	82075060	10
424034	Hole saw 105mm (4.1/8")	5051074240347	82075060	10
424035	Hole saw 111mm (4.3/8")	5051074240354	82075060	10
424036	Hole saw 114mm (4.1/2")	5051074240361	82075060	10
424037	Arbor with 8mm Hex Drive & 1/4" Pilot drill, for use with hole saws up to 30mm	5051074240378	82075060	10
424038	Arbor with 11mm Hex Drive & 1/4" Pilot drill, for use with hole saws up to 30mm	5051074240385	82075060	10
424039	Quick release Arbor with 11mm Hex Drive, 1/4" Pilot drill and fixing pins, for use with hole saws from 32 to 150mm	5051074240392	82075060	10
424040	Heavy duty Arbor with 11mm Hex Drive, 1/4" Pilot drill, fixing pins and locking plate, for use with hole saws from 32 to 150mm	5051074240408	82075060	10
424041	Replacement 1/4" Pilot drill bit for use with Arbor 424037	5051074240415	82075060	10
424042	Replacement 1/4" Pilot drill bit for use with Arbors 424038, 424039, 424040 and special arbor in kit 424043	5051074240422	82075060	10
424043	Nine piece Hole saw kit containing: Hole saws in sizes 22, 29, 35, 44, 51 and 64mm, Arbors 424040 & special arbor (similar to 424037) plus 4mm hex key	5051074240439	82075060	10
424044	Six piece Hole saw kit containing: Hole saws in sizes 40, 54, 65, 67, and 68mm plus Arbor 424039	5051074240446	82075060	10
424045	Electricians Hole saw set containing: Hole saws in sizes 16, 20, 25, 32, 38 and 51mm, Arbors 424037 & 42039 plus 4mm hex key	5051074240453	82075060	10
424046	Downlighter Hole saw set containing: 65, 70, 76 and 83mm, Arbor 424039 plus 4mm Hex key	5051074240460	82075060	10
424047	Arbor with SDS Drive & 1/4" Pilot drill, for use with hole saws up to 30mm	5051074240477	82075060	10
424048	Quick release Arbor with SDS Drive, 1/4" Pilot drill and fixing pins, for use with hole saws from 32 to 150mm	5051074240484	82075060	10
424049	300mm extension drive for all 11mm shaft arbors, complete with shaft locking grub screw	5051074240491	82075060	10
400002	Stocked display stand	5051074000026	73262080	1

Technical product information	Maximum cut depth for all sizes – 38mm
Standards compliance	None applicable
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Hole saws are guaranteed for life against imperfect materials or workmanship Over time cutting tools will wear, such wear is not covered under the terms of the warranty Damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
300002	510	190	870	3700				
303001	490	5	850	560				
424001	16	16	56	30	36	16	116	32
424002	19	19	50	25	36	19	110	37
424003	20	20	50	45	36	20	110	47
424005	22	22	50	48	36	22	110	50
424006	25	25	50	50.5	36	25	110	52.5
424007	29	29	50	75	36	29	110	77
424008	32	32	50	80	36	32	110	85
424010	38	38	50	115	38	38	110	120
424011	40	40	50	130	40	40	110	135
424012	41	41	50	135	41	41	110	140
424013	43	43	43	88	43	43	103	93
424014	44	44	43	90	44	44	103	95
424015	48	48	43	110	48	48	103	115
424016	51	51	43	115	51	51	103	120
424017	54	54	43	130	54	54	103	135
424018	57	57	43	145	57	57	103	150
424019	60	60	43	155	60	60	103	160
424020	64	64	43	175	64	64	103	180
424021	65	65	43	177	65	65	103	182
424022	67	67	43	195	67	67	103	200
424024	70	70	43	205	70	70	103	210
424025	73	73	43	230	73	73	103	235
424026	76	76	43	260	76	76	103	265
424027	79	79	43	283	79	79	103	288
424028	83	83	43	305	83	83	103	310
424029	86	86	43	310	86	86	103	315
424030	89	89	43	315	89	89	103	320
424031	92	92	43	350	92	92	103	355
424032	95	95	43	370	95	95	103	375
424033	102	102	43	408	102	102	103	413

424034	105	105	43	433	105	105	103	438
424035	111	111	43	495	111	111	103	500
424036	114	114	43	500	114	114	103	505
424037	17	17	110	60	45	45	125	100
424038	17	17	110	65	45	45	125	105
424039	40	40	110	150	45	45	120	190
424040	35	35	115	215	45	45	132	255
424041	5	5	81	20	37	11	145	25
424042	5	5	102	25	37	11	145	30
424043	–	–	–	–	250	220	60	1290
424044	–	–	–	–	250	220	60	1277
424045	–	–	–	–	245	60	210	1045
424046	–	–	–	–	320	65	250	1705
424047	20	20	150	95	165	45	45	130
424048	40	40	150	170	165	45	45	210
424049	20	20	300	315	35	20	360	323

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
300002						
303001						
424001	121	197	67	500		
424002	121	197	67	520		
424003	121	197	67	540		
424005	121	197	67	620		
424006	121	197	67	760		
424007	121	197	67	960		
424008	115	264	112	1140		
424010	115	264	112	1480		
424011	115	264	112	1580		
424012	115	264	112	1680		
424013	115	264	112	1470		
424014	115	264	112	1260		
424015	115	264	112	1500		
424016	115	264	112	1540		

424017	115	485	91	1800		
424018	115	485	91	2020		
424019	115	485	91	2100		
424020	115	485	91	2340		
424021	115	485	91	2420		
424022	115	485	91	2480		
424024	115	485	91	2740		
424025	115	485	91	2880		
424026	115	485	91	3000		
424027	161	521	106	3200		
424028	161	521	106	3400		
424029	161	521	106	3600		
424030	161	521	106	3900		
424031	161	521	106	3900		
424032	161	521	106	4120		
424033	161	521	106	4880		
424034	152	639	136	4500		
424035	152	639	136	5400		
424036	152	639	136	5600		
424037	139	230	97	1140		
424038	139	230	97	1180		
424039	139	230	97	2060		
424040	139	230	97	2700		
424041	252	309	145	6000		
424042	252	309	145	7100		
424043	255	439	318	1370		
424044	255	439	318	1350		
424045	255	439	318	1350		
424046	267	658	215	7500		
424047	139	230	97	1240		
424048	139	230	97	2000		
424049	167	367	58	2500		

Packaging waste details

Item	Primary Packaging				Secondary packaging (shelf box + any other material not used in display)			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
300002								
303001								
424001	6	Hanger	1	Label	12	Protective bags	63	Box
424002	6	Hanger	1	Label	12	Protective bags	63	Box
424003	6	Hanger	1	Label	12	Protective bags	63	Box
424005	6	Hanger	1	Label	12	Protective bags	63	Box
424006	6	Hanger	1	Label	12	Protective bags	63	Box
424007	6	Hanger	1	Label	12	Protective bags	63	Box
424008	6	Hanger	1	Label	13	Protective bags	86	Box
424010	6	Hanger	1	Label	13	Protective bags	86	Box
424011	6	Hanger	1	Label	13	Protective bags	86	Box
424012	6	Hanger	1	Label	13	Protective bags	86	Box
424013	6	Hanger	1	Label	13	Protective bags	86	Box
424014	6	Hanger	1	Label	13	Protective bags	86	Box
424015	6	Hanger	1	Label	13	Protective bags	86	Box
424016	6	Hanger	1	Label	13	Protective bags	86	Box
424017	6	Hanger	1	Label	14	Protective bags	110	Box
424018	6	Hanger	1	Label	14	Protective bags	110	Box
424019	6	Hanger	1	Label	14	Protective bags	110	Box
424020	6	Hanger	1	Label	14	Protective bags	110	Box
424021	6	Hanger	1	Label	14	Protective bags	110	Box
424022	6	Hanger	1	Label	14	Protective bags	110	Box
424024	6	Hanger	1	Label	14	Protective bags	110	Box
424025	6	Hanger	1	Label	14	Protective bags	110	Box
424026	6	Hanger	1	Label	14	Protective bags	110	Box
424027	6	Hanger	1	Label	15	Protective bags	201	Box
424028	6	Hanger	1	Label	15	Protective bags	201	Box
424029	6	Hanger	1	Label	15	Protective bags	201	Box
424030	6	Hanger	1	Label	15	Protective bags	201	Box
424031	6	Hanger	1	Label	15	Protective bags	201	Box
424032	6	Hanger	1	Label	15	Protective bags	201	Box
424033	6	Hanger	1	Label	15	Protective bags	201	Box

424034	6	Hanger	1	Label	16	Protective bags	253	Box
424035	6	Hanger	1	Label	16	Protective bags	253	Box
424036	6	Hanger	1	Label	16	Protective bags	253	Box
424037	40.5	Hanger	1	Label			86	Box
424038	40.5	Hanger	1	Label			86	Box
424039	40.5	Hanger	1	Label			86	Box
424040	40.5	Hanger	1	Label			86	Box
424041	6.9	Hanger	1	Label			230	Box
424042	6.9	Hanger	1	Label			230	Box
424043	448.5	Box	1	Label			600	Box
424044	448.5	Box	1	Label			600	Box
424045	448.5	Box	1	Label			600	Box
424046	575	Box	1	Label			700	Box
424047	42	Hanger	1	Label			86	Box
424048	42	Hnager	1	Label			86	Box
424049	7.2	Hanger	1	Label			92	Box