

Terminals

KLS 10



- Rated connecting capacity: 2,5-16 mm², Cu

- for insertion in cable junction boxes
- current carrying capacity: 63 A
- 5-pole per pole 6 x 2.5 mm² sol, 4 x 4 mm² sol, 4 x 6 mm² sol, 4 x 10 mm² sol, 2 x 16 mm² s
- for cable junction boxes K 8100, K 9100, KF 4100, KF 5100, KF 8100, KF 9100, KD 5100, KD 4100
- complete with fixing elements

rated insulation voltage	Ui = 690 V a.c./d.c.
Dismantling length	11 mm
tightening torque for terminal	2,0 Nm
Weight	0,138 kg

Drawings

Dimension drawing

