

### General Information

Extended Product Type:	BJM10
Product ID:	1SNA173611R2100
EAN:	3472591736113
Catalog Description:	BJM 10 2 POLES Jumper Bars
Long Description:	BJM10 - Jumper Bars - 2 poles -- 10mm Spacing

### Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

### Ordering

EAN:	3472591736113
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

### Dimensions

Product Net Weight:	5 g
---------------------	-----

### Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.05 kg
Package Level 1 EAN:	3472591736113
Package Level 2 Units:	1000 piece
Package Level 2 Width:	175 mm
Package Level 2 Height:	130 mm
Package Level 2 Length:	227 mm
Package Level 3 Units:	180000 piece
Product Packing Type:	Bag

### Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJM
Product Name:	Jumper Bar
Rated Current (I <sub>n</sub> ):	Main Circuit 57 A
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
RoHS Information:	1SND230492F0201

### Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

