

Housing - HC-B 24-SMQ-84/O2PG29 - 1678431


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base, with double locking latch, height 84 mm, without screw connection, 2x Pg29



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 151959
Weight per Piece (excluding packing)	477.53 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	84 mm
Width	57 mm
Length	144 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B24, BB46, BBB64, D64, DD108, M
Type	B24
Housing type	Box mounting bases
Locking type	With double locking latch
No. of cable outlets	2
Cable exit	Lateral
Screw connection	none
Type of the screw connection	2x Pg29
Housing material	Aluminum die-cast

Housing - HC-B 24-SMQ-84/O2PG29 - 1678431

Technical data

General

Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Housing - HC-B 24-SMQ-84/O2PG29 - 1678431

Approvals

Approval details

EAC

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG29-M68N-PNES-GY - 1411146



Cable gland, Cable gland material: Polyamide, External cable diameter 18 mm ... 25 mm, Shielding: No, Connecting thread: Pg29, Color: silver grey

Cable gland - G-INS-PG29-M68N-NNES-S - 1411176



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 18 mm ... 25 mm, Shielding: No, Connecting thread: Pg29, Color: silver

Cable gland - G-INSEC-PG29-M68N-NNES-S - 1411201



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 18 mm ... 25 mm, Shielding: Yes, Connecting thread: Pg29, Color: silver

Plug for cable screw gland

Filler plugs - HC-BS-PG29 - 1674532



Filler plugs, for Pg screw connections, type Pg29

Drawings

Housing - HC-B 24-SMQ-84/O2PG29 - 1678431

Dimensioned drawing

