

Product Information



MONO

5025PJH080L51-10 RAL9006

EAN 4031582308440

Swivel castor with wheel brake, housing made of Polyamide, with blind hole for furniture fittings. Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, with threadguards, plain bearing



Technical Data

Wheel diameter	80 mm
Width of Tread	24 mm
Centre hole	10 mm
Offset	34 mm
Swivel Interference	180 mm
Overall height	104 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.125 kg
Hardness of tread	A 87 Shore
Load capacity	70 kg
Load capacity (static)	140 kg

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



MONO

5025PJH080L51-10 RAL9006

EAN 4031582308440

