

## Grommet - HC-DR-PG29 - 1686601


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Notched seals/2 washers, for pressure screws, type Pg29



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 189822
Weight per Piece (excluding packing)	11.39 g
Custom tariff number	40169300
Country of origin	Germany

### Technical data

#### Dimensions

External cable diameter	18 mm ... 27 mm
-------------------------	-----------------

#### Ambient conditions

Degree of protection	IP65
	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

#### General

Cable seal material	Perbunan
Thread type on connection side	Pg29

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109

# Grommet - HC-DR-PG29 - 1686601

## Classifications

### eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109

### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC002498
ETIM 5.0	EC002498

### UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

---