

Pipe Wrench S-Type






With fast adjustment



83 60 010



- Time-saving, precise adjustment of the opening width at the press of a button directly on the workpiece
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Chrome vanadium electric steel, forged, oil-hardened

No.	EAN 4003773-	 Ø mm	 Ø Inch	Inside dia. mm	 Inch	Clamping width mm	 mm	 g
83 60 010	075424	42	1 5/8	25	1	42	330	955