




LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			G1	REVISED PER ECO-11-004917	11MAR11	RK HMR



- 1 . INSULATION DIA .170 MAX
- 2 . FITS TAB .032 THK



100	LOOSE PC,BOX	8-640915-1
-	TAPE MOUNTED	640915-2
-	LOOSE PIECE	640915-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
-

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
BODY,BRASS .016
SLV,NYLON,COLOR, BLUE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .015
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
BODY,TIN

DWN L OLMEDA 26JUN95
CHK M ELLIS 26JUN95
APVD B BARE 26JUN95
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

TE Connectivity

RECEPTACLE, 205 SERIES,
FASTON, PIDG,
WIRE SIZE, 16-14 AWG

SIZE A3
CAGE CODE 00779
DRAWING NO C-640915

RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS
SHEET 1 OF 1
REV G1

1470-19 (3/11)