



Sample photo

Order symbol: P 081606
Product nbr: 7094170
Description: Enclosure
Remarks: Polyester

EAN: 6418074004352
El. number:
 Finland 3423657
 Denmark 8212005620
 Italy 7331020
 Sweden 2536209

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		75	160	55	Ingress Protection (EN 60529): IP 66/67
inch:		3	6.3	2.2	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		GRP			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7001			UV resistance: UL 508
Cover colour:		RAL 7001			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-50 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-60 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
PM 0816		Mounting plate			
PRM 0816		DIN-15 Mounting rail			
TRM 0816		DIN-15 Mounting rail			
TRH 1216		DIN-35 Mounting rail			
MRS 28540		Wall fastening lug set			

